

EKI-2525P EKI-2525SPI EKI-2526PI

5-port Industrial PoE Switch 5-port Industrial PoE Switch with 1x100Fx Single-Mode and Wide Temperature 6-port Industrial PoE Switch with Wide Temperature



Features

- Provides 5/6 Fast Ethernet ports with 4 PoE ports with injector function
- Provides 1 x 100Mbps Single-mode SC type fiber optic port (EKI-2525SPI)
- Supports 10/100Mbps Auto Negotiation
- Provides broadcast storm protection
- Supports Ethernet ESD protection
- Provides Slim size, DIN-rail/Wallmount with IP30 metal mechanism
- Supports Redundant 48 V_{DC} power input and P-Fail relay
- Supports operating temperatures from -10 ~ 60° C (EKI-2525P)
- Supports wide operating temperature -40 ~ 75° C (EKI-2525SPI/EKI-2526PI)

Introduction

The EKI-2525P/EKI-2525SPI is a 5-port unmanaged PoE (Power-over-Ethernet) Industrial Ethernet switch and EKI-2526PI is a 6-port unmanaged PoE Industrial Ethernet switch, they support 4 PoE ports which are classified as power source equipments (PSE). The PoE devoces makes centralized power supply come true and provides up to 15.4 watts of power per port. Advantech EKI PoE devices can be used to power IEEE802.3af compliant powered devices (PD) by Ethernet cable and eliminates the need for additional power wiring. Advantech EKI PoE devices come equipped with all the standard features of the EKI family. Furthermore, it offers a 48 V_{DC} redundant power input design (EKI-2525P/EKI-2526PI), and is secured with a double protection mechanism; Power Polarity Reverse Protect and an Overload Current Resettable Fuse. Advantech EKI PoE devices come with compact metal housing that rates IP30 to help against from dusty industrial environments.

Specifications

Communications

- Standard** IEEE 802.3, 802.3u, 802.3x, 802.3af
- LAN** 10/100Base-T(X)
- Transmission Distance** Ethernet: Up to 100 m (EKI-2525P/EKI-2526PI)
Single-mode Fiber: Up to 30km (EKI-2525SPI)
- Transmission Speed** Up to 100 Mbps

Fiber Optics (EKI-2525SPI)

- Signal Mode** 1310nm
Tx Power: -8/-15 dBm
Rx Sensitivity: -34dBm
Parameters: 9/125um

Interface

- Connectors** PoE Ports: 4 (Ports 1 ~ 4)
Ethernet x1 (EKI-2525P)
1xSC type fiber connector(EKI-2525SPI)
Ethernet x2 (EKI-2526PI)
6-pin removable screw terminal (power & relay)
P1, P2, P-Fail
- LED Indicators** 10/100TX: Link/Activity, Duplex/Collision

Power

- Power Consumption** EKI-2525P: 65 W (Full load PoE)
EKI-2525SPI: 62.5 W (Full load PoE)
EKI-2526PI: 62.6 W (Full load PoE)
- Power Input** 48 V_{DC} (EKI-2525P/EKI-2526PI), redundant dual inputs
24/48 V_{DC} (EKI-2525PA), redundant dual inputs
- Power Output** 15.4 W at 48V (per PoE port)
- Fault Output** 1 Relay Output

Mechanism

- Dimensions (W x H x D)** 37 x 140 x 95 mm (EKI-2525P/EKI-2525SPI)
48.6 x 140 x 95 mm (EKI-2526PI)
- Enclosure** IP30, Metal shell with solid mounting kits
- Mounting** DIN-rail, Panel

Protection

- Reverse Polarity** Present
- Overload** EKI-2525P: 3 A @ 48 V_{DC}
EKI-2525SPI: 3 A @ 48 V_{DC}
EKI-2526PI: 3.5 A @ 48 V_{DC}

Environment

- Operating Temperature** -10 ~ 60° C (14 ~ 140° F) (EKI-2525P)
Wide temp. model -40 ~ 75° C (-40 ~ 167° F) (EKI-2525SPI/EKI-2526PI)
- Storage Temperature** -40 ~ 85° C (-40 ~ 185° F)
- Operating Humidity** 5 ~ 95% (non-condensing)
- Storage Humidity** 0 ~ 95% (non-condensing)
- MTBF** 440,132 hrs

Certifications

- Safety** UL 60950-1, CAN/CSA-C22.2 No.60950
- EMC** U.S.A.: FCC Part 15 CISPR 22
EU: EN55011, EN61000-6-4
EN55022 Class A,
EN55024
IEC61000-4-2/3/4/5/6/8
EN61000-6-2
- Shock** IEC60068-2-27
- Freefall** IEC60068-2-32
- Vibration** IEC60068-2-6

Ordering Information

- EKI-2525P** 5-port PoE Switch
- EKI-2525SPI** 5-port PoE Switch w/ 1-port 100Fx SM/ Wide Temp
- EKI-2526PI** 6-port PoE Switch w/ Wide Temp