


Heat Shrinkable Spade Type Crimp Connectors



Shrinking Temperature: $\geq 150^{\circ}\text{C}$
Operating Temperature: $-40^{\circ}\text{C} \sim 120^{\circ}\text{C}$
Shrinking Ratio: 3:1
Terminal Body: Copper
Insulation: PE
Plating: Tin

Best.-Nr.	Typ	Wire Range mm ² /Awg	STUD SIZE	DIMENSION					COLOR
				d2 (mm)	W (mm)	L (mm)	Dø (mm)	d1ø (mm)	
				±0.1	±0.1	±1.0	±0.3	±0.2	
73 64 63	231032Y	0.5~1.5mm ² 22-16AWG	M3	3.2	5.7	30.5	4.8	1.7	RED
73 64 89	231137Y		M3.5	3.7	5.7	30.5	4.8	1.7	
73 89 98	231043Y		M4	4.3	6.4	30.5	4.8	1.7	
73 90 50	231053Y		M5	5.3	8.1	30.5	4.8	1.7	
73 65 25	231164Y		M6	6.4	12.0	36.5	4.8	1.7	
73 65 74	232032Y	1.5~2.5mm ² 16-14AWG	M3	3.2	5.7	30.5	5.8	2.3	BLUE
73 66 08	232137Y		M3.5	3.7	5.7	30.5	5.8	2.3	
73 90 17	232043Y		M4	4.3	6.4	30.5	5.8	2.3	
73 90 68	232053Y		M5	5.3	8.1	30.5	5.8	2.3	
73 66 44	232164Y		M6	6.4	12.0	36.5	5.8	2.3	
73 66 88	233037Y	4~6mm ² 10-12AWG	M3.5	3.7	8.3	36.0	6.8	3.4	YELLOW
73 90 35	233043Y		M4	4.3	8.3	36.0	6.8	3.4	
73 90 83	233053Y		M5	5.3	9.0	36.0	6.8	3.4	
73 67 20	233064Y		M6	6.4	12.0	41.0	6.8	3.4	