

A-510 ラッチ式ハンドル

ラッチ式平面ハンドル

LATCH TYPE FLUSH HANDLES

ソフトな操作 非常用安全機構付

PAT.PEND.



A-510
アルミニウム製

特 徴 Feature

- 三方締めで大きな扉もガッチリと閉まります。
- 高級感のあるデザイン
- ゴムパッキンによる防塵構造
- ワンタッチ開閉
- 右用・左用(本図・写真共右用です)
- Three-point securing enables a large door to easily lock.
- High-grade image design.
- With a dustproof rubber packing.
- One-touch locking / unlocking
- The left-hand or right-hand use. (drawings and photo show the right-hand use)

- 仕 様 ●材 質: アルミニウム合金(ADC)
●表面仕上: サチライトクロムめっき(MACr)
●付 属 品: キー2本
- 用 途 ●大型配分電盤・筐体のワンタッチ開閉に最適
- 納 期 ●標準品・・・納期お問合せください
- 備 考 ●No.500キー・マスター方式の組込みはお問合せください。
●ロッド棒(AC-25-R)・ラッチ(C-40)と組合せてご使用ください。
●右用・左用をご指定ください。

- Specifi- ●Material: Aluminum alloy (ADC)
cations ●Finish: Satellite chrome plating (MACr)
●Accessories: Two keys
- Specifi- ●One-touch locking / unlocking door for
use large power / distribution boards and cases.
- Remarks ●Use rod (AC-25-R) and latch (C-40) together.
●Specify the left-hand or right-hand use.



A-510-1-1-R


A-510-3-1-R




キーNo.0200
Key




裏面(安全機構付)
Rear (with safety mechanism)



パネル穴明け寸法 Panel drilling dimensions



使用例 Example of application



内部からの解錠もできます。
Can be unlocked from inside.

商品番号 Product No.	RoHS	CAD	備 考 Remarks	L1	(L2)	L3	L4	L5	L6	(W1)	W2	(W3)	W4	W5	W6	H1	(H2)	H3	H4	(H5)	R	製品質量(g) Mass	コード Code	単 価 Price	量販価格 Bulk Price
A-510-1-1-L	●		鍵付き With lock	77	13.5	60	22	175	165	70	91.5	9.2	27	12.5	81	29	34	9	23	63	12	832	01797	¥6,700	5個～ ¥6,432
A-510-1-1-R	●	2D/3D																					01798		5個～ ¥6,432
A-510-2-1-L	●		鍵付き With lock	100	6.5	60	18	166	157	70	71.5	9.2	30	12.5	61	28	36.5	7	22	62	9	705	01799	¥5,600	5個～ ¥5,376
A-510-2-1-R	●	2D																					01800		5個～ ¥5,376
A-510-3-1-L	●		鍵付き With lock	100	7	50	18	134.5	127	70	69	10.5	30	12.5	61	28	36.5	5	22	62	9	615	01801	¥5,300	5個～ ¥5,088
A-510-3-1-R	●	2D																					01802		5個～ ¥5,088

●: RoHS指令対応品 ▲: RoHS指令に対応可能です。

※大量のご注文は更にお安くなります。