



RH40M Series

Motorized Impeller

Ø 404mm Backward Curved

- Backward curved centrifugal fans feature extremely long blades. These impellers are highly resistant to dirt and dust. Their hydraulic efficiency is very high.
- Impeller completely made of a welded steel design.
- Maintenance-free ball bearings.
- Direction of rotation is CW as seen from inlet of the impeller.
- UL, CSA, VDE approvals on some models, please contact application engineering.
- Recommended inlet ring: IR/265500.

Part Number	Curve	CFM @ 0	VAC	Hertz	Power (W)	dBA	Max Amb. Temp C	Bearing Type	Features	Capacitor (µF)	Wgt. (lbs)
RH40M-6/206522	1	1640	115	60	300	65	50	Ball	Leads	30	16.1
RH40M-4/105553	2	2800	115	60	680	73	40	Ball	Leads	50	19.1
RH40M-6/111192	1	1640	230	60	300	65	50	Ball	Leads	8	16.1
RH40M-4/203473	2	2800	230	60	680	73	40	Ball	Leads	12	19.1

