



FEATURES:

- Ideal for temporary connection between terminals, wire wrap posts and test equipment.
- Banana Plug is vertically stackable and cross stackable.
- Banana Plug will mate to Model #5259, 1581 or any standard Banana Jack.

MATERIALS:

Connector: 1st End – Minipincer Test Clip

Material: Selectively gold plated Beryllium Copper contact.

Insulation: Nylon

Wire: 20 AWG, 41 x 36 t.c., PVC insulated, 2.2 (.087) O.D.

Marking: "POMONA 5421-XX-***"

Connector: 2nd End – Stacking Banana Plug

Material: Brass Body, Beryllium Copper spring, nickel plated.

Insulation: Polypropylene

RATINGS:

Operating Temperature.: +55°C. (+ 131°F.) Max.

Voltage: Hand-held testing: 30 VAC/60 VDC Max.

Hands free testing in controlled voltage environments: 300 WVDC

Current: 5 Amperes

ORDERING INFORMATION: Model 5421-XX-*

XX = Cable Lengths, Standard Lengths: 12" (305), 18" (457), 24" (610) 36" (914), 48" (1219) & 60" (1524).

Additional lengths can be quoted upon request.

*= Color, -0 Black, -2 Red

Ordering Example: 5421-60-2 Indicates 60" in length, Color is Red.

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies.

Made in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

[5421-12-2](#) [5421-12-0](#) [5421-48-0](#) [5421-48-2](#) [5421-24-0](#) [5421-24-2](#) [5421-36-0](#) [5421-36-2](#)