

Item # ATV312HU22M2, Variable Speed Drive



Variable Speed Drive
Variable Speed Drive

SPECIFICATIONS

Family	Altivar 312
Product Line	AC Drives
Output Ampere Rating	11
Application	Constant Torque
Enclosure Rating	IP20
Frame Size	7
HP Rating	3
kW Rating	2.2
Voltage Rating	208/240VAC
Input Phase	1 Phase
Output Phase	3 Phase
Control Voltage	24Vdc
Logic Input	6
Analog Input	3

Analog Output	1
Logic/Relay Outputs	1 Form C, 1 NO
Weight [lb]	5.18
Weight [kg]	2.35
UL File No.	E116875
CSA File	1464725
Other	CE, GOST, RoHS, NOM, EMITECH
Communication	Modbus and CANopen

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[ATV312HU22M2](#)