

Day/Night Zoom Bullet Camera



- High resolution 500TV lines in colour
- Vandal resistant housing
- 10 x Optical Zoom
- Selectable 2 x, 4 x, 8 x Digital Zoom or OFF
- TRUE Day/Night, Mechanical Cut-Filter
- 33-piece Infra-Red LED Assembly with CDS Sensor
- On Screen Display (OSD) Menu
- DNR (Digital Noise Reduction) - 4 levels of noise reduction
- Saves up to 70% HDD Storage with DNR, using MPEG Codec
- Selectable electronic shutter control, FLK/ESC/Manual
- Selectable white balance, ATW/AWC/Manual
- Selectable back light compensation, H/M/L/Off
- Selectable gain control, H/M/L/Off
- Sens-up - maintains luminance levels in low light x128
- Privacy masking - 4 programmable zones
- Mirror function - horizontal image inversion
- Camera Title
- IP67 rated
- Dual Voltage, DC12V/AC24V
- Fully Cable Managed Bracket
- Sunshield

Image Sensor	Sony 1/4" Super HAD CCD
	500 TVL Colour
Horizontal Resolution	570 TVL Monochrome
Effective Pixels	752 (h) x 582 (v)
Video Output	CVBS 1.0V p-p ~ 75Ω
	ESC (x128, 1/50 to 1/20,000 sec.)
	Manual (x128, 1/50 to 100,000 sec.)
Electronic Shutter	Flickerless - 1/100 Sec.
	10 x Optical Zoom (3.8-38.0mm F1.8 to F2.8)
Lens	Selectable 8 x Digital Zoom (Off/x2/x4/x8)
	H: Approx. 51.2° (Wide) to 5.58° (Tele)
Angle of View	V: Approx. 39.3° (Wide) to 4.27° (Tele)
LED	33-piece LED Assembly with CDS Photosensor
Power consumption	800mA Max. with IR LEDs ON using DC12V
Power supply	12V dc or 24V ac
Dimensions (DiameterxH)	145x100mm
Operating temperature	-10°C — 50°C
Weight	900g

450295.450232

Description	Order Code	Price Each
Camera	129-4899●	
Remote Control	129-4900●	