

# Type PSU AC Motor Start Capacitors

## Non-polarized, Aluminum Electrolytic AC Motor Start Capacitors



### Optional Enhancements

End Caps

Mounting Bracket



Motor Start Resistor



The Type PSU is a compact non-polar, dual voltage rated, AC motor start capacitor constructed in a round rugged bakelite case. To extend the life of relay contact switches, the PSU can be purchased with optional bleeder resistors assembled with 1/4" quick-connect terminals. An optional mounting system consisting of a bracket that is attached to the capacitor case with one end cap is available. The PL end caps are for use with wiring through the bracket to the motor and the PLA end caps are for off motor mounting.

### Highlights

- ♦ Dual quick-connect terminals
- ♦ Rugged bakelite case
- ♦ Compact Size
- ♦ Resistor options
- ♦ Mounting options
- ♦ Non-polar
- ♦ Meets EIA RS-463 Type 2 (Normal Performance)
- ♦ Listed under UL file no. E128034

### Specifications



Complies with the EU Directive 2002/95/EC requirement restricting the use of Lead (Pb), Mercury (Hg), Cadmium (Cd), Hexavalent chromium (Cr(VI)), PolyBrominated Biphenyls (PBB) and PolyBrominated Diphenyl Ethers (PBDE).

**Capacitance Range:**

**Voltage Range**

**Capacitance Tolerance:**

**Operating Temperature Range:**

**Storage Temperature Range:**

**Operating Frequency:**

**Power Factor:**

21  $\mu$ F to 1280  $\mu$ F

110 Vac to 330 Vac

See ratings table

-40 °C to 65 °C

-55 °C to 85 °C

50 Hz to 60 Hz

10% max (12%  $\leq$  30  $\mu$ F)

### Ratings

| Cap<br>( $\mu$ F) | Catalog<br>Part Number | Voltage<br>(Vac) | Case<br>Code | Diameter<br>$\pm$ .015<br>(Inches) | Length<br>$\pm$ .06<br>(Inches) |
|-------------------|------------------------|------------------|--------------|------------------------------------|---------------------------------|
| 21-25             | PSU2115                | 110/125          | 1            | 1 7/16                             | 2 3/4                           |
| 25-30             | PSU2515                | 110/125          | 1            | 1 7/16                             | 2 3/4                           |
| 30-36             | PSU3015                | 110/125          | 1            | 1 7/16                             | 2 3/4                           |
| 36-43             | PSU3615                | 110/125          | 1            | 1 7/16                             | 2 3/4                           |
| 43-52             | PSU4315                | 110/125          | 1            | 1 7/16                             | 2 3/4                           |
| 47-56             | PSU4715                | 110/125          | 1            | 1 7/16                             | 2 3/4                           |
| 53-64             | PSU5315                | 110/125          | 1            | 1 7/16                             | 2 3/4                           |
| 64-77             | PSU6415                | 110/125          | 1            | 1 7/16                             | 2 3/4                           |
| 72-86             | PSU7215                | 110/125          | 1            | 1 7/16                             | 2 3/4                           |
| 88-106            | PSU8815                | 110/125          | 1            | 1 7/16                             | 2 3/4                           |
| 108-130           | PSU10815               | 110/125          | 1            | 1 7/16                             | 2 3/4                           |
| 124-149           | PSU12415               | 110/125          | 1            | 1 7/16                             | 2 3/4                           |
| 130-156           | PSU13015               | 110/125          | 1            | 1 7/16                             | 2 3/4                           |
| 145-174           | PSU14515               | 110/125          | 1            | 1 7/16                             | 2 3/4                           |
| 161-193           | PSU16115               | 110/125          | 1            | 1 7/16                             | 2 3/4                           |
| 189-227           | PSU18915A              | 110/125          | 1            | 1 7/16                             | 2 3/4                           |
| 200-240           | PSU20015               | 110/125          | 2            | 1 7/16                             | 3 3/8                           |

| Cap<br>( $\mu$ F) | Catalog<br>Part Number | Voltage<br>(Vac) | Case<br>Code | Diameter<br>$\pm$ .015<br>(Inches) | Length<br>$\pm$ .06<br>(Inches) |
|-------------------|------------------------|------------------|--------------|------------------------------------|---------------------------------|
| 216-259           | PSU21615               | 110/125          | 2            | 1 7/16                             | 3 3/8                           |
| 216-259           | PSU21615A              | 110/125          | 1            | 1 7/16                             | 2 3/4                           |
| 233-280           | PSU23315A              | 110/125          | 2            | 1 7/16                             | 3 3/8                           |
| 233-280           | PSU23315B              | 110/125          | 1            | 1 7/16                             | 2 3/4                           |
| 243-292           | PSU24315A              | 110/125          | 2            | 1 7/16                             | 3 3/8                           |
| 243-292           | PSU24315B              | 110/125          | 1            | 1 7/16                             | 2 3/4                           |
| 270-324           | PSU27015A              | 110/125          | 2            | 1 7/16                             | 3 3/8                           |
| 270-324           | PSU27015B              | 110/125          | 1            | 1 7/16                             | 2 3/4                           |
| 300-360           | PSU30015               | 110/125          | 4            | 1 13/16                            | 3 3/8                           |
| 324-389           | PSU32415A              | 110/125          | 3            | 1 7/16                             | 4 3/8                           |
| 324-389           | PSU32415B              | 110/125          | 1            | 1 7/16                             | 2 3/4                           |
| 340-408           | PSU34015               | 110/125          | 4            | 1 13/16                            | 3 3/8                           |
| 340-408           | PSU34015A              | 110/125          | 2            | 1 7/16                             | 3 3/8                           |
| 378-454           | PSU37815               | 110/125          | 4            | 1 13/16                            | 3 3/8                           |
| 378-454           | PSU37815A              | 110/125          | 2            | 1 7/16                             | 3 3/8                           |
| 400-480           | PSU40015               | 110/125          | 4            | 1 13/16                            | 3 3/8                           |
| 400-480           | PSU40015A              | 110/125          | 2            | 1 7/16                             | 3 3/8                           |

See page 5.00 for capacitor hardware and resistor options.

# Type PSU AC Motor Start Capacitors

## Ratings

| Cap<br>( $\mu$ F) | Catalog<br>Part Number | Voltage<br>(Vac) | Case<br>Code | Diameter<br>$\pm 0.015$<br>(Inches) | Length<br>$\pm 0.06$<br>(Inches) |
|-------------------|------------------------|------------------|--------------|-------------------------------------|----------------------------------|
| 430-516           | PSU43015A              | 110/125          | 4            | 1 13/16                             | 3 3/8                            |
| 430-516           | PSU43015B              | 110/125          | 2            | 1 7/16                              | 3 3/8                            |
| 460-552           | PSU46015A              | 110/125          | 4            | 1 13/16                             | 3 3/8                            |
| 460-552           | PSU46015B              | 110/125          | 2            | 1 7/16                              | 3 3/8                            |
| 540-648           | PSU54015A              | 110/125          | 4            | 1 13/16                             | 3 3/8                            |
| 540-648           | PSU54015B              | 110/125          | 5            | 1 13/16                             | 4 3/8                            |
| 590-708           | PSU59015A              | 110/125          | 5            | 1 13/16                             | 4 3/8                            |
| 590-708           | PSU59015B              | 110/125          | 4            | 1 13/16                             | 3 3/8                            |
| 645-774           | PSU64515               | 110/125          | 5            | 1 13/16                             | 4 3/8                            |
| 645-774           | PSU64515A              | 110/125          | 4            | 1 13/16                             | 3 3/8                            |
| 708-850           | PSU70815               | 110/125          | 5            | 1 13/16                             | 4 3/8                            |
| 708-850           | PSU70815A              | 110/125          | 4            | 1 13/16                             | 3 3/8                            |
| 720-864           | PSU72015               | 110/125          | 5            | 1 13/16                             | 4 3/8                            |
| 720-864           | PSU72015A              | 110/125          | 4            | 1 13/16                             | 3 3/8                            |
| 800-960           | PSU80015               | 110/125          | 5            | 1 13/16                             | 4 3/8                            |
| 800-960           | PSU80015A              | 110/125          | 4            | 1 13/16                             | 3 3/8                            |
| 815-978           | PSU81515               | 110/125          | 5            | 1 13/16                             | 4 3/8                            |
| 815-978           | PSU81515A              | 110/125          | 4            | 1 13/16                             | 3 3/8                            |
| 829-995           | PSU82915A              | 110/125          | 5            | 1 13/16                             | 4 3/8                            |
| 829-995           | PSU82915B              | 110/125          | 4            | 1 13/16                             | 3 3/8                            |
| 850-1020          | PSU85015               | 110/125          | 5            | 1 13/16                             | 4 3/8                            |
| 850-1020          | PSU85015A              | 110/125          | 4            | 1 13/16                             | 3 3/8                            |
| 1000-1200         | PSU100015A             | 110/125          | 7            | 2 1/16                              | 4 3/8                            |
| 1020-1224         | PSU102015              | 110/125          | 7            | 2 1/16                              | 4 3/8                            |
| 1175-1410         | PSU117515              | 110/125          | 7            | 2 1/16                              | 4 3/8                            |
| 1280-1536         | PSU128015              | 110/125          | 7            | 2 1/16                              | 4 3/8                            |
| 21-25             | PSU2165A               | 165              | 1            | 1 7/16                              | 2 3/4                            |
| 25-30             | PSU2565A               | 165              | 1            | 1 7/16                              | 2 3/4                            |
| 30-36             | PSU3065A               | 165              | 1            | 1 7/16                              | 2 3/4                            |
| 36-43             | PSU3665A               | 165              | 1            | 1 7/16                              | 2 3/4                            |
| 43-52             | PSU4365A               | 165              | 1            | 1 7/16                              | 2 3/4                            |
| 47-56             | PSU4765A               | 165              | 1            | 1 7/16                              | 2 3/4                            |
| 53-64             | PSU5365A               | 165              | 1            | 1 7/16                              | 2 3/4                            |
| 64-77             | PSU6465A               | 165              | 1            | 1 7/16                              | 2 3/4                            |
| 72-86             | PSU7265A               | 165              | 1            | 1 7/16                              | 2 3/4                            |
| 88-106            | PSU8865                | 165              | 2            | 1 7/16                              | 3 3/8                            |
| 88-106            | PSU8865A               | 165              | 1            | 1 7/16                              | 2 3/4                            |
| 108-130           | PSU10865               | 165              | 2            | 1 7/16                              | 3 3/8                            |
| 108-130           | PSU10865A              | 165              | 1            | 1 7/16                              | 2 3/4                            |
| 124-149           | PSU12465               | 165              | 2            | 1 7/16                              | 3 3/8                            |
| 124-149           | PSU12465A              | 165              | 1            | 1 7/16                              | 2 3/4                            |
| 130-156           | PSU13065               | 165              | 2            | 1 7/16                              | 3 3/8                            |
| 130-156           | PSU13065A              | 165              | 1            | 1 7/16                              | 2 3/4                            |
| 145-174           | PSU14565               | 165              | 2            | 1 7/16                              | 3 3/8                            |
| 145-174           | PSU14565A              | 165              | 1            | 1 7/16                              | 2 3/4                            |
| 161-193           | PSU16165               | 165              | 2            | 1 7/16                              | 3 3/8                            |
| 161-193           | PSU16165A              | 165              | 1            | 1 7/16                              | 2 3/4                            |

| Cap<br>( $\mu$ F) | Catalog<br>Part Number | Voltage<br>(Vac) | Case<br>Code | Diameter<br>$\pm 0.015$<br>(Inches) | Length<br>$\pm 0.06$<br>(Inches) |
|-------------------|------------------------|------------------|--------------|-------------------------------------|----------------------------------|
| 189-227           | PSU18965B              | 165              | 2            | 1 7/16                              | 3 3/8                            |
| 189-227           | PSU18965C              | 165              | 1            | 1 7/16                              | 2 3/4                            |
| 216-259           | PSU21665A              | 165              | 4            | 1 13/16                             | 3 3/8                            |
| 233-280           | PSU23365               | 165              | 3            | 1 7/16                              | 4 3/8                            |
| 233-280           | PSU23365A              | 165              | 4            | 1 13/16                             | 3 3/8                            |
| 243-292           | PSU24365               | 165              | 3            | 1 7/16                              | 4 3/8                            |
| 243-292           | PSU24365A              | 165              | 4            | 1 13/16                             | 3 3/8                            |
| 270-324           | PSU27065A              | 165              | 3            | 1 7/16                              | 4 3/8                            |
| 270-324           | PSU27065B              | 165              | 4            | 1 13/16                             | 3 3/8                            |
| 324-389           | PSU32465               | 165              | 5            | 1 13/16                             | 4 3/8                            |
| 324-389           | PSU32465A              | 165              | 4            | 1 13/16                             | 3 3/8                            |
| 340-408           | PSU34065               | 165              | 5            | 1 13/16                             | 4 3/8                            |
| 340-408           | PSU34065A              | 165              | 4            | 1 13/16                             | 3 3/8                            |
| 378-454           | PSU37865               | 165              | 5            | 1 13/16                             | 4 3/8                            |
| 378-454           | PSU37865A              | 165              | 4            | 1 13/16                             | 3 3/8                            |
| 400-480           | PSU40065               | 165              | 5            | 1 13/16                             | 4 3/8                            |
| 400-480           | PSU40065A              | 165              | 4            | 1 13/16                             | 3 3/8                            |
| 430-516           | PSU43065               | 165              | 5            | 1 13/16                             | 4 3/8                            |
| 430-516           | PSU43065A              | 165              | 4            | 1 13/16                             | 3 3/8                            |
| 460-552           | PSU46065               | 165              | 5            | 1 13/16                             | 4 3/8                            |
| 460-552           | PSU46065A              | 165              | 4            | 1 13/16                             | 3 3/8                            |
| 540-648           | PSU54065               | 165              | 7            | 2 1/16                              | 4 3/8                            |
| 540-648           | PSU54065A              | 165              | 4            | 1 13/16                             | 3 3/8                            |
| 21-25             | PSU2135                | 220/250          | 1            | 1 7/16                              | 2 3/4                            |
| 25-30             | PSU2535                | 220/250          | 1            | 1 7/16                              | 2 3/4                            |
| 30-36             | PSU3035                | 220/250          | 1            | 1 7/16                              | 2 3/4                            |
| 36-43             | PSU3635                | 220/250          | 1            | 1 7/16                              | 2 3/4                            |
| 43-52             | PSU4335B               | 220/250          | 2            | 1 7/16                              | 3 3/8                            |
| 43-52             | PSU4335C               | 220/250          | 1            | 1 7/16                              | 2 3/4                            |
| 47-56             | PSU4735                | 220/250          | 2            | 1 7/16                              | 3 3/8                            |
| 47-56             | PSU4735A               | 220/250          | 1            | 1 7/16                              | 2 3/4                            |
| 53-64             | PSU5335                | 220/250          | 2            | 1 7/16                              | 3 3/8                            |
| 53-64             | PSU5335A               | 220/250          | 1            | 1 7/16                              | 2 3/4                            |
| 64-77             | PSU6435                | 220/250          | 2            | 1 7/16                              | 3 3/8                            |
| 64-77             | PSU6435A               | 220/250          | 1            | 1 7/16                              | 2 3/4                            |
| 72-86             | PSU7235                | 220/250          | 4            | 1 13/16                             | 3 3/8                            |
| 88-106            | PSU8835                | 220/250          | 4            | 1 13/16                             | 3 3/8                            |
| 108-130           | PSU10835A              | 220/250          | 4            | 1 13/16                             | 3 3/8                            |
| 124-149           | PSU12435               | 220/250          | 5            | 1 13/16                             | 4 3/8                            |
| 124-149           | PSU12435A              | 220/250          | 4            | 1 13/16                             | 3 3/8                            |
| 130-156           | PSU13035               | 220/250          | 5            | 1 13/16                             | 4 3/8                            |
| 130-156           | PSU13035A              | 220/250          | 4            | 1 13/16                             | 3 3/8                            |
| 145-174           | PSU14535               | 220/250          | 5            | 1 13/16                             | 4 3/8                            |
| 145-174           | PSU14535A              | 220/250          | 4            | 1 13/16                             | 3 3/8                            |
| 161-193           | PSU16135A              | 220/250          | 7            | 2 1/16                              | 4 3/8                            |
| 189-227           | PSU18935A              | 220/250          | 7            | 2 1/16                              | 4 3/8                            |
| 189-227           | PSU18935B              | 220/250          | 6            | 2 1/16                              | 3 3/8                            |

See page 5.000 for capacitor hardware and resistor options.

# Type PSU AC Motor Start Capacitors


## Ratings

| Cap<br>( $\mu$ F) | Catalog<br>Part Number | Voltage<br>(Vac) | Case<br>Code | Diameter<br>$\pm 0.015$<br>(Inches) | Length<br>$\pm 0.06$<br>(Inches) |
|-------------------|------------------------|------------------|--------------|-------------------------------------|----------------------------------|
| 216-259           | PSU21635A              | 220/250          | 7            | 2 1/16                              | 4 3/8                            |
| 216-259           | PSU21635B              | 220/250          | 6            | 2 1/16                              | 3 3/8                            |
| 233-280           | PSU23335A              | 220/250          | 7            | 2 1/16                              | 4 3/8                            |
| 233-280           | PSU23335B              | 220/250          | 6            | 2 1/16                              | 3 3/8                            |
| 243-292           | PSU24335               | 220/250          | 7            | 2 1/16                              | 4 3/8                            |
| 243-292           | PSU24335A              | 220/250          | 6            | 2 1/16                              | 3 3/8                            |
| 270-324           | PSU27035A              | 220/250          | 7            | 2 1/16                              | 4 3/8                            |
| 270-324           | PSU27035B              | 220/250          | 6            | 2 1/16                              | 3 3/8                            |
| 16-20             | PSU1630                | 330              | 2            | 1 7/16                              | 3 3/8                            |
| 18-22             | PSU1830                | 330              | 4            | 1 13/16                             | 3 3/8                            |
| 21-25             | PSU2130                | 330              | 1            | 1 7/16                              | 2 3/4                            |
| 21-25             | PSU2130A               | 330              | 2            | 1 7/16                              | 3 3/8                            |
| 25-30             | PSU2530                | 330              | 2            | 1 7/16                              | 3 3/8                            |
| 30-36             | PSU3030                | 330              | 2            | 1 7/16                              | 3 3/8                            |
| 36-43             | PSU3630                | 330              | 2            | 1 7/16                              | 3 3/8                            |
| 43-52             | PSU4330                | 330              | 2            | 1 7/16                              | 3 3/8                            |
| 43-52             | PSU4330A               | 330              | 4            | 1 13/16                             | 3 3/8                            |
| 47-56             | PSU4730                | 330              | 4            | 1 13/16                             | 3 3/8                            |
| 53-64             | PSU5330B               | 330              | 4            | 1 13/16                             | 3 3/8                            |
| 64-77             | PSU6430                | 330              | 4            | 1 13/16                             | 3 3/8                            |


| Cap<br>( $\mu$ F) | Catalog<br>Part Number | Voltage<br>(Vac) | Case<br>Code | Diameter<br>$\pm 0.015$<br>(Inches) | Length<br>$\pm 0.06$<br>(Inches) |
|-------------------|------------------------|------------------|--------------|-------------------------------------|----------------------------------|
| 72-86             | PSU7230B               | 330              | 5            | 1 13/16                             | 4 3/8                            |
| 72-86             | PSU7230C               | 330              | 4            | 1 13/16                             | 3 3/8                            |
| 88-106            | PSU8830A               | 330              | 5            | 1 13/16                             | 4 3/8                            |
| 88-106            | PSU8830B               | 330              | 4            | 1 13/16                             | 3 3/8                            |
| 108-130           | PSU10830B              | 330              | 7            | 2 1/16                              | 4 3/8                            |
| 124-149           | PSU12430               | 330              | 8            | 2 9/16                              | 4 3/8                            |
| 124-149           | PSU12430A              | 330              | 7            | 2 1/16                              | 4 3/8                            |
| 130-156           | PSU13030               | 330              | 7            | 2 1/16                              | 4 3/8                            |
| 145-174           | PSU14530A              | 330              | 7            | 2 1/16                              | 4 3/8                            |
| 161-193           | PSU16130               | 330              | 8            | 2 9/16                              | 4 3/8                            |
| 161-193           | PSU16130A              | 330              | 7            | 2 1/16                              | 4 3/8                            |
| 189-227           | PSU18930               | 330              | 8            | 2 9/16                              | 4 3/8                            |
| 189-227           | PSU18930A              | 330              | 7            | 2 1/16                              | 4 3/8                            |
| 216-259           | PSU21630               | 330              | 8            | 2 9/16                              | 4 3/8                            |
| 216-259           | PSU21630A              | 330              | 7            | 2 1/16                              | 4 3/8                            |
| 270-324           | PSU27030               | 330              | 8            | 2 9/16                              | 4 3/8                            |
| 270-324           | PSU27030A              | 330              | 7            | 2 1/16                              | 4 3/8                            |
| 378-454           | PSU37830               | 330              | 8            | 2 9/16                              | 4 3/8                            |
| 460-552           | PSU46030               | 330              | 8            | 2 9/16                              | 4 3/8                            |

See page 5.000 for capacitor hardware and resistor options.

| Case<br>Code | Inches               |                       |             |
|--------------|----------------------|-----------------------|-------------|
|              | D<br>( $\pm 0.015$ ) | L<br>(+0.020, -0.030) | C<br>(Ref.) |
| 1            | 1-7/16 (1.4375)      | 2-3/4 (2.750)         | 1/2 (.500)  |
| 2            | 1-7/16 (1.4375)      | 3-3/8 (3.375)         | 1/2 (.500)  |
| 3            | 1-7/16 (1.4375)      | 4-3/8 (4.375)         | 1/2 (.500)  |
| 4            | 1-13/16 (1.8125)     | 3-3/8 (3.375)         | 5/8 (.625)  |
| 5            | 1-13/16 (1.8125)     | 4-3/8 (4.375)         | 5/8 (.625)  |
| 6            | 2-1/16 (2.0625)      | 3-3/8 (3.375)         | 7/8 (.875)  |
| 7            | 2-1/16 (2.0625)      | 4-3/8 (4.375)         | 7/8 (.875)  |
| 8            | 2-9/16 (2.5625)      | 4-3/8 (4.375)         | 7/8 (.875)  |



Single Disconnect Terminals  
(SQC)  
(All Cases)



## Type PSU AC Motor Start Capacitors

---

**Notice and Disclaimer:** All product drawings, descriptions, specifications, statements, information and data (collectively, the "Information") in this datasheet or other publication are subject to change. The customer is responsible for checking, confirming and verifying the extent to which the Information contained in this datasheet or other publication is applicable to an order at the time the order is placed. All Information given herein is believed to be accurate and reliable, but it is presented without any guarantee, warranty, representation or responsibility of any kind, expressed or implied. Statements of suitability for certain applications are based on the knowledge that the Cornell Dubilier company providing such statements ("Cornell Dubilier") has of operating conditions that such Cornell Dubilier company regards as typical for such applications, but are not intended to constitute any guarantee, warranty or representation regarding any such matter – and Cornell Dubilier specifically and expressly disclaims any guarantee, warranty or representation concerning the suitability for a specific customer application, use, storage, transportation, or operating environment. The Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by Cornell Dubilier with reference to the use of any Cornell Dubilier products is given gratis (unless otherwise specified by Cornell Dubilier), and Cornell Dubilier assumes no obligation or liability for the advice given or results obtained. Although Cornell Dubilier strives to apply the most stringent quality and safety standards regarding the design and manufacturing of its products, in light of the current state of the art, isolated component failures may still occur. Accordingly, customer applications which require a high degree of reliability or safety should employ suitable designs or other safeguards (such as installation of protective circuitry or redundancies or other appropriate protective measures) in order to ensure that the failure of an electrical component does not result in a risk of personal injury or property damage. Although all product-related warnings, cautions and notes must be observed, the customer should not assume that all safety measures are indicated in such warnings, cautions and notes, or that other safety measures may not be required.