

HCMOS/TTL COMPATIBLE VOLTAGE CONTROL CRYSTAL OSCILLATOR

ASV/ASV1 SERIES

*RoHS COMPLIANT



7.0 x 5.08 x 1.8mm

FEATURES:

- Leadless chip carrier (LCC), Low profile.
- HCMOS/TTL Compatible, 3.3Vdc, 2.5Vdc, & 1.8Vdc operation.
- Seam welding, Reflow capable.
- Seam welding, 1.4 max. height (ASV1)


APPLICATIONS:

- Provide clock signals for microprocessors, PC mainboards, Graphic cards.
- High output drive capability applications.

STANDARD SPECIFICATIONS:

PARAMETERS	
Frequency Range:	1.000 MHz to 150 MHz
Operating Temperature:	-10° C to + 70° C (see options)
Storage Temperature:	- 55° C to + 125° C
Overall Frequency Stability:	± 100 ppm max. (see options)
Supply Voltage (Vdd):	3.3 Vdc ± 10% (see options)
Input Current:	See Table 1
Symmetry:	40/60 % max.@ 1/2Vdd (see options)
Rise And Fall Time (Tr/tf):	See Table 1
Output Load:	15 pF (5TTL)
Output Voltage:	VOH = 0.9 * Vdd min. VOL = 0.4 Vdc max.
Start-up Time:	10ms max.
Tristate Function :	"1" (VIH >= 2.2 Vdc) or open: Oscillation "0" (VIL < 0.8 Vdc) : Hi Z
Aging At 25°c/year :	± 5ppm max.
Period Jitter One Sigma :	± 25ps max.
Disable Current:	15µA max.

OUTLINE DRAWING:



MARKING:

- XX.X RS (see note)
- ASV ZYW (see note)

Alternate Marking:

Marking scheme subject to change without notice.
Contact factory for Alternate Marking Specifications.

NOTE:

XX.X First 3 digits of freq.
ex: 66.6 or 100
R Freq. Stability option (*)
S Duty cycle option (*)
L Temperature option (*)
Z month A to L
Y year 6 for 2006
W traceability code (A to Z)

PIN	FUNCTION
1	Tri-state
2	GND/Case
3	Output
4	Vdd

Table 1

Freq. (MHz)	Idd max. (mA)	Tr/Tf max. (nSec)
1.0 ~ 34.99	16	10ns
35.0 ~ 60.0	25	5ns
60.01~99.99	40	5ns
100 ~ 150	50	2.5ns

OPTIONS AND PART IDENTIFICATION (Left blank if standard):

ASV - Voltage - Frequency - Temp. - Overall Frequency Stability - Duty cycle - Packaging

Freq Stability options:

Y for ± 10 ppm max.
J for ± 20 ppm max.
R for ± 25 ppm max.
K for ± 30 ppm max.
H for ± 35 ppm max.
C for ± 50 ppm max.

Temperature options:

I for 0°C to +50°C
D for -10°C to +60°C
E for -20°C to +70°C
F for -30°C to +70°C
N for -30°C to +85°C
L for -40°C to +85°C

Voltage options:

25 for 2.5V
18 for 1.8V

Symmetry option:

S for 45/55% at 1/2Vdd
S1 for 45/55% at 1.4Vdc

Packaging option:

T for Tape and Reel (1,000pcs/reel)
T5 for Tape and Reel (500pcs/reel)

