




DESCRIPTION: 45° ENTRY - DIE CAST



SPECIFICATION:

MATERIAL:

BACKSHELL: ZINC, NICKEL PLATED,
COPPER UNDER PLATE
HOUSING SCREW: STEEL, ZINC PLATED
COMPRESSON INSERT: ABS, UL94-HB

OPERATING TEMPERATURE: -40°C TO +120°C

BACKSHELL KIT INCLUDES:

- (2) BACKSHELL HALVES
 - (2) MOUNTING SCREWS
 - (1) PLASTIC INSERTS TREE (4-SETS)
- DIAMETERS: 0.157 [4.00], 0.167 [5.00], 0.276 [7.00], 0.354 [9.00]

954-YYY-030R121

SERIES _____
POSITIONS _____
009 _____
015 _____
025 _____
037 _____
MATERIAL _____
030 = DIE CAST (NICKEL)
RoHS COMPLIANT _____
R = HIGH TEMP. PROCESS
COLOR _____
12 = NICKEL OVER COPPER
PUT-UP _____
1 = KIT

DIMENSIONS (IN.)					
No. OF PINS	A	B	C	D	E
09	1.429	0.571	0.984	1.220	0.512
	36.30	14.50	24.99	31.00	13.00
15	1.587	0.571	1.312	1.555	0.512
	40.30	14.50	33.32	39.50	13.00
25	1.587	0.571	1.852	2.094	0.512
	40.30	14.50	47.04	53.20	13.00
37	1.587	0.571	2.500	2.744	0.512
	40.30	14.50	63.50	69.70	13.00

DO NOT SCALE FROM DRAWING



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OF SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:
C. SMITH

CHECKED:

DATE:
03-30-07

DATE:

NorComp

SCALE:
1 : 1

SHEET
1

OF
1

REV
2

DWG NO.
954-YYY-030R121

RoHS COMPLIANT