



Dimensions: mm (in.)



SWITCH FUNCTION



POS. 1	POS. 2	POS. 3
ON	OFF	ON
2-3		2-1
	OPEN	



RECOMMENDED MOUNTING



SOLDER LUG

Electrical Specifications:

- Electrical life: 50,000 make-and-break cycles at full load
- Contact resistance: 10m Ω max. initial @ 2-4VDC 100mA
- Insulation resistance: 1,000M Ω min.
- Dielectric strength: 1000V RMS @ sea level
- Rating: 5A/120VAC or 28VDC, 2A/250VAC

Mechanical Specifications:

- Operating temperature: -30°C to 85°C
- Circuit: SPDT On-Off-On

Note:

- RoHS compliant by exemption

Materials:

- Case: Diallyl phthalate (DAP)
- Actuator: Nylon, black std.
- Bushing: Brass, nickel plated
- Housing: Stainless Steel
- Switch support: Brass, tin plated
- Fixed terminal: Silver plated copper alloy
- Movable contact: Silver plated copper alloy

Miniature Rocker Switch
103-7135-EVX

Mountain
Switch

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mountain Switch:](#)

[103-7135-EVX](#)