





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	H3	REVISED PER ECO-11-004587	11MAR11	RK	HMR
	J	REVISED PER ECR-16-017870	20APR2017	BDA	MZ



PERIPHERAL SEAL
BONDED IN PLACE
SEE TABLE



RECOMMENDED PANEL CUTOUT
SCALE 2:1



FREE HANGING

STANDARD	YES	4-40 BRASS THREADED INSERT	20	FLANGED	5 206433-6
SMALL PACK	NO	.125 DIA	20	FLANGED	206433-5
STANDARD	NO	.125 DIA	20DF WITHOUT INSULATION SUPPORT	FLANGED	5 206433-4
STANDARD	NO	4-40 BRASS THREADED INSERT	20	FLANGED	206433-3
STANDARD	NO	-	20	FREE HANGING	206433-2
STANDARD	NO	.125 DIA	20	FLANGED	206433-1
PACKAGING	PERIPHERAL SEAL	A	WILL ACCEPT SOCKET CONTACT SIZE	TYPE	PART NUMBER

- 1 CONTACT CAVITIES IDENTIFIED BY CHARACTERS ON FRONT AND REAR FACE.
- 2 AMP MOLDED ON THIS SURFACE.
- 3 PART NUMBER AND DATE CODE MARKED ON THIS SURFACE.
- 4 206433-4 STRIPPED WIRE LENGTH SHOULD BE .193-.213 WITH .095 MAX INSULATION.
- 5 OBSOLETE PART NUMBER.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J.McCLINTON 1-25-88	TE Connectivity		
DIMENSIONS: INCHES		CHK R.STONE 1-26-88			
		APVD M.KAPEZYNSKI 1-27-88	NAME RECEPTACLE ASSEMBLY, ARRANGEMENT 11-8 REVERSE SEX, CPC		
		PRODUCT SPEC			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC	SIZE A2		
MATERIAL NYLON, GLASS FILLED, FLAME RETARDED, BLACK		WEIGHT -	CAGE CODE 00779		
FINISH -		CUSTOMER DRAWING	DRAWING NO C-206433		
		SCALE 4:1	SHEET 1 OF 1		
			REV J		