


LOC	DIST	P	F	REVISIONS			DATE	APPD
				ZONE	LTR	DESCRIPTION		
G	86				P	REV PER 0G3A-0561-01	070CT02	JR MS



1 CIRCULAR MIL RANGE: 190,000-231,000 CM

325602

PART NO

DO NOT SCALE PRINT.
UNLESS SPECIFIED
DIMENSIONS IN mm [INCHES]
TOLERANCES ON :
2 PLC DEC ± 0.51[.020]
3 PLC DEC ± -
ANGLES ± -
MATERIAL
COPPER ASTM B-75
ANNEALED
FINISH
TIN PLATE
0.00381[.000150] MIN
THK PER MIL-T-10727

DR 02/28/90
DK SCHRUM
CHK 08/12/92
AJ KAUFMAN
APPD 08/12/92
WJ VOCKROTH
APPD 08/12/92
CR RHODS
PRODUCT SPEC
-
APPLICATION SPEC
-
WEIGHT
-

AMP

AMP Incorporated
Harrisburg, PA 17105-3608

NAME
TERMINAL, RECTANGULAR TONGUE,
AMPOWERTM,
WIRE SIZE: 105.0mm²[4/0] AWG

SIZE	CAGE CODE	DRAWING NO
C	00779	C-325602
SCALE	2:1	SHEET 1 OF 1

THIS DRAWING IS A CONTROLLED DOCUMENT FOR
AMP INCORPORATED. IT IS SUBJECT TO CHANGE
AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.