

Welded Tip Thermocouples PFA Insulated Leads



- Fast response, exposed junction
- Thermocouple types K&T to IEC 584 (BS EN60584)
- PFA, twin twist insulated wires with bare wire tails
- Conductors 1/0.2mm
- Rated -75°C to 250°C
- Ideal for test & development applications

	Farnell Code	Labfacility Stock Code
Type K, 3 metre lead	163-3481	Z2 - K - 3M
Type K, 5 metre lead	163-3482	Z2 - K - 5M
Type T, 3 metre lead	163-3483	Z2 - T - 3M
Type T, 5 metre lead	163-3484	Z2 - T - 5M