

# Multi-Position/Miniature Slide/PC SLS Series

## MATERIAL SPECIFICATIONS:

Contacts ..... Silver plate over copper alloy  
 Case Material ..... Steel  
 Actuator Material ..... Polycarbonate  
 Terminals/Fixed Contacts ..... Silver plate over brass  
 Terminal Seal ..... Epoxy



## TYPICAL PERFORMANCE CHARACTERISTICS:

Contact Rating ..... 250 mA @ 125 VAC, 150 mA @ 12 VDC  
 Initial Contact Resistance ..... 30 Milliohms max.  
 Contact Timing ..... Break before make  
 Insulation Resistance ..... 500 Megohms min.  
 Dielectric Strength ..... 500 VAC  
 Actuation Force ..... 250 Grams + 150 - 100  
 Actuator Travel ..... .126" (3.20)  
 Life Expectancy ..... 10,000 Cycles

## ENVIRONMENTAL SPECIFICATIONS:

Operating Temperature ..... 14°F to +140°F (-10°C to +60°C)  
 Storage Temperature ..... 14°F to +140°F (-10°C to +60°C)


## 2 TO 6 POSITIONS



SLS250PC



SLS220PC



SLS240PCA





SLS230PC

Model	Type	Dim.A	Dim.B
SLS220PC	2 Positions	.272(6.91)	.535(13.59)
SLS230PC	3 Positions	.398(10.11)	.661(16.79)
SLS240PC	4 Positions	.524(13.31)	.787(19.99)
SLS250PC	5 Positions	.650(16.51)	.913(23.19)
SLS260PC	6 Positions	.776(19.71)	1.039(26.39)

# Multi-Position/PC Terminals/Silver Plate Contacts Standard SL Series


## 2 TO 10 POSITIONS



SL660  
(with KSS KNOB)



SL550



SL770

Model	Type	Dim. A	Dim. B	Dim. C	Knob Model	Description	Dim. D	Dim. E
SL220	2 Positions	.95(24.13)	.750(19.05)	.750(19.05)	KSS10A	Aluminum-Clear Anodize	.270(6.86)	.500(12.70)
SL330	3 Positions	1.11(28.19)	.910(23.1)	.910(23.1)	KSS10B	Aluminum-Black Anodize	.270(6.86)	.500(12.70)
SL550	5 Positions	1.42(36.07)	1.22(30.99)	1.22(31.1)	KSS20A	Aluminum-Clear Anodize	.305(7.75)	.512(13.00)
SL660	6 Positions	1.58(40.13)	1.38(35.05)	1.38(35.1)	KSS20B	Aluminum-Black Anodize	.305(7.75)	.512(13.00)
SL770	7 Positions	1.74(44.20)	1.54(39.12)	1.54(39.1)				
SL880	8 Positions	1.89(48.01)	1.70(43.18)	1.70(43.1)				
SL1000	10 Positions	2.21(56.13)	2.01(51.05)	2.01(51.5)				

Need more technical information?  
 Consult your local Augat sales office  
 listed on the back cover