

Screw plug


10xx M/G

Configuration

Screw plug	Brass CuZn39Pb3, nickel-plated
O-ring	Nitrile rubber
Connecting thread	Pg as per DIN 40430

Properties

Temperature range	for secure sealing of unused threaded or clearance hole -30°C +100°C
Protection grade	IP68



Features

round

A	L	H	Da		Part No.
	mm	mm	mm	Piece	
Pg 7	4,5	7	16	100	1007 M/G
Pg 9	4,5	8	19	100	1009 M/G
Pg 11	4,5	8	22	100	1011 M/G
Pg 13,5	6	10	24	100	1013 M/G
Pg 16	6	10	26	100	1016 M/G
Pg 21	6,5	10	32	100	1021 M/G
Pg 29	8	12	39	50	1029 M/G
Pg 36	9	15	50	25	1036 M/G
Pg 42	10	16	57	25	1042 M/G
Pg 48	10	16	64	10	1048 M/G

hexagonal

A	L	SW1	H		Part No.
	mm	mm	mm	Piece	
Pg 7	5	14	8	100	10.607 M/G

A	L	SW1	H		Part No.
	mm	mm	mm	Piece	
Pg 9	6	17	9	100	10.609 M/G
Pg 11	6	20	9	100	10.611 M/G
Pg 13,5	6,5	22	9,5	100	10.613 M/G
Pg 16	6,5	24	9,5	100	10.616 M/G
Pg 21	7	30	11	100	10.621 M/G
Pg 29	8	40	12	50	10.629 M/G
Pg 36	9	50	15	25	10.636 M/G