

PRODUCT DATASHEET

VERSATILE

- Four lighting modes
 - High Bright Spot
 - Low Bright Spot
 - White Flood Light
 - Green Light for inspection



CONVENIENT

- Dedicated Green/White switches
- Pivots to aim light where you need it
- Adjustable elastic headband with handy pencil holder



WEATHERPROOF

- Meets IEC 60529 IPX4 standards
- Continues to operate after exposure to splashing water from all directions



BRIGHT

- Powerful LED provides 70 lumens in Spot mode
- Useable light for 6 hours in Spot mode. Using Energizer® MAX® batteries



INHD5L32H

Lightweight, versatile and comfortable, the Energizer® Brilliant Beam® Industrial® 5 LED Headlight is perfect for any job that requires both hands. It puts light where you are looking and has a swivel adjustment with ratchet positioning for accurate aim.

Variable light sources allow you to choose the best illumination for the job – flood, spot or green – without changing lights. Also, this light can be worn comfortably around the head for long periods of time.




Before Using Your Flashlight:
Please read all instructions and cautionary markings on the package and light

Brilliant Beam® Headlight **Energizer®** **INDUSTRIAL**

Product Detail:

Designation:	Energizer Industrial Brilliant Beam Headlight
Model:	INHD5L32H
Color:	Yellow
Power Source:	Three "AAA"
ANSI/NEDA:	Series 24
Lamp:	3 White LEDs, 2 Green LEDs
Lamp Life (hr):	Lifetime
Lamp Output (lumens):	70 - Spot, 34 - Low, 25 - Flood
Beam Distance (m):	77 - Spot, 45 - Low, 25 - Flood
Peak Beam Intensity (cd):	1,482 - Spot, 506 - Low, 156 - Flood
Run Time (h:mm):	6 - Spot, 18 - Low Spot
Typical Weight:	107 grams with 3 Alkaline AAA batteries 71.7 grams without batteries
Dimensions (mm):	45 x 63 x 42

Performance:



Tested according to ANSI/NEMA FL 1 Standards.

Important Notice

This datasheet contains information specific to products manufactured at the time of its publication
Contents herein do not constitute a warranty
©Energizer / All Rights Reserved