



MALE FACE VIEW					
3 POLE		4 POLE		5 POLE	
Pin No.	Wire	Pin No.	Wire	Pin No.	Wire
1	Brown	1	Brown	1	Brown
2	—	2	White	2	White
3	Blue	3	Blue	3	Blue
4	Black	4	Black	4	Black
				5	Grey



POLE	MATERIAL NUMBER	ENGINEERING NUMBER
3	1200310004	4R3F06E02C3003
4	1200310006	4R4F06E02C3003
5	1200310027	4R5F06E02C3003

CONNECTOR SPECIFICATION:	
VOLTAGE RATING	3-4POL:60V/AC 75V/DC 5POL:30V/AC 36V/DC
AMPERAGE RATING	3 AMPS
PROTECTION	IP67
OPERATING TEMPERATURE	-25°C TO +90°C

ITEM	COMPONENT	MATERIAL	FINISH
1	INSERT	POLYURETHANE (PUR)	BLACK
2	CONTACT SOCKET	COPPER ALLOY	GOLD OVER NICKEL
3	SHELL	BRASS	NICKEL PLATED
4	LOCKNUT	BRASS	NICKEL PLATED
5	O-RING	VITON	BLACK
6	COPPER STRANDING AWG24/0.25mm ²	JACKET: PVC	

DESCRIPTION EC NO: WEU2010-0338 DRWN: REISSNER 2010/02/18 CHKD: RE APPR: FPACHER 2010/02/24	DESCRIPTION	QUALITY SYMBOLS ▽ = 0 ▽C = 0	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE MM ONLY		SCALE 2:1	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION			
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		mm	INCH	DRAWN BY REISSNER	DATE 2010/02/18	NC-XP-M-REC-0.3M AWG24-PVC FRONT MOUNT				
				4 PLACES	±---	±---	CHECKED BY FP	DATE 2010/02/18					
				3 PLACES	±---	±---	APPROVED BY FPACHER		DATE 2010/02/19		 MOLEX INCORPORATED		
				2 PLACES	±---	±---	MATERIAL NO.		DOCUMENT NO.			SD-120090-027	
				1 PLACE	±0.1	±---	SEE TABLE		SHEET NO. 1 OF 1				
			ANGULAR ± --- °			SIZE A3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					