





Quartz Crystal

MHz range

SMD-version

model	KX – 7
frequency	25,0 MHz
mode	fundamental
operating temperature	0° ~ + 85°C
frequency tolerance at +25°C	± 10 ppm
temperature tolerance -0° ~ + 85°C	± 15 ppm
load capacitance C_L	18 pF
series resonance R_1 max.	40 Ohm
aging (first year)	± 2 ppm
shunt capacitance C_O max.	5,0 pF
drive level in mW max.	0,05
RoHS	since production start
contents of reel	1000 pcs.
part no.	12.88772



(mm) reel diameter 178 mm