



T50L0UVC2

Standard Cable Tie, 15.35" Long, 50lb Tensile Strength, PA66UV, Black, 100/pkg

Article Number: 112-05460

Part Number: T50L0UVC2

Type: T50L



Base Data

Part No.	T50L0UVC2
Type	T50L
Color	Black (BK)
Features	• UV stabilized cable ties contain an inhibitor which prolongs the life of the tie in UV exposures . • Inside serrations allow for strong hold on cables and wire bundles. • Head design provides high tensile strength with very low insertion force. • Bent tail ensures a quick and simple installation.
Application Method	Quick, simple fixing by hand or with HellermannTyton tensioning tools
Identification Plate Position	none
Releasable Closure (Yes/No)	No
Tie Closure	plastic pawl
Typical Application	Used to bundle and secure wire and cable.
Variant	Inside Serrated

Product Dimensions

Min. Tensile Strength	50.0lbs / 225.0N
Length (L)	15.35" / 390.0mm
Width (W) (imperial)	0.18"
Width (W)	4.7mm

Min. Ø Bundle	0.06" / 1.5mm
Max. Ø Bundle	4.3" / 110.0mm
Thickness	1.2mm

Material and Specifications

Material	Polyamide 6.6 UV-resistant (PA66UV)
US MILSPEC	MS3367-2-0
Flammability	UL94 V2
Material Specification	HF
Operating Temperature	-40 °F to +185 °F (-40 °C to +85 °C)
ROHS Conformity	 RoHS
Specification	MIL 53421
UL Listed (US and Canada)	No
UL Recognized (US and Canada)	No

Logistic and Packaging

Packaging Type	pc
Pkg. Qty.	100
Carton Qty.	5000
EAN code	4031026108087
UPC	089306179733