

Combination spanner, offset, 111M/

- Set of combination spanners, offset in Metric sizes
- DIN 3113 / ISO 3318 / ISO 7738
- Finish: Nickel and chrome-plated, fine-polished
- Material: VANADIUM-EXTRA
- Open-end angle 15°, box end 15° offset, equal openings at both ends, short type
- With Dynamic-Drive-Profile
- T = sets in black plastic wallet
- 111M/S6 and 111M/10 in attractive sales cardboard box
- 111M/SH6 and SH12 on a functional black plastic holder flexible for wall or to carry by handle with a locking function of the spanners



111M/7T	1828882	1	7	8 10 13 14 17 19 22	575
111M/11T	1828899	1	11	8 9 10 11 12 13 14 15 17 19 22	740
111M/14T	1828905	1	14	6 8 9 10 13 14 15 17 19 22 24 27 30 32	2270
111M/17T	1828912	1	17	6 7 8 9 10 11 12 13 14 15 16 17 18 19 20 21 22	1615
111M/26T	1828929	1	26	6 7 8 9 10 11 12 13 14 15 16 17 18 19 20 21 22 23 24 25 26 27 28 29 30 32	4355
111M/10	1828936	1	10	8 9 10 11 12 13 14 17 19 22	960
111M/SH6	3013279	1	6	8 10 12 13 14 17	338
111M/SH12	3013347	1	12	8 9 10 11 12 13 14 15 16 17 18 19	1050

	
111M/7T 8 10 13 14 17 19 22mm	
111M/11T 8 9 10 11 12 13 14 15 17 19 22mm	
111M/14T 6 8 9 10 13 14 15 17 19 22 24 27 30 32mm	
111M/17T 6 7 8 9 10 11 12 13 14 15 16 17 18 19 20 21 22mm	
111M/26T 6 7 8 9 10 11 12 13 14 15 16 17 18 19 20 21 22 23 24 25 26 27 28 29 30 32mm	
111M/10 8 9 10 11 12 13 14 17 19 22	
111M/SH6 8 10 12 13 14 17mm	
111M/SH12 8 9 10 11 12 13 14 15 16 17 18 19mm	