



Sample photo

Order symbol: PCM 200/63 G
Product nbr: 6016324
Description: Enclosure, PC
Remarks: Grey cover

EAN: 6418074051950
El. number:
Finland: 3435270
Denmark: 8212027446
Sweden: 2535342
Norway:

Including: Base with metric knock-outs and TPE gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Dimensions:			Length	Width	Height	Rating:
mm:	255	180	63			Ingress Protection (EN 60529): IP 66/67
inch:	10.0	7.1	2.5			Impact Resistance (EN 62262): IK 08
Materials:						Electrical insulation: Totally insulated
Material:	Polycarbonate					Halogen free (DIN/VDE 0472, Part 815): Yes
Base colour:	RAL 7035					UV resistance: UL 508
Cover colour:	RAL 7035					Flammability Rating (UL 746 C 5): UL 746C 5V
Cover screws material:	Polyamide					Glow Wire Test (IEC 695-2-1) °C: 960
Cover screws colour:	Grey					NEMA Class: NEMA 1, 4, 4X, 6, 12, 13
Gasket material:	TPE					
Temperatures:						Certificates:
Short term:	-40 ... 120 °C					Germanischer Lloyd (GL)
Continuous:	-40 ... 80 °C					Underwriters Laboratories
Short term:	-40 ... 250 °F					Det Norske Veritas
Continuous:	-40 ... 175 °F					Fimko
Accessories:						Europe EN 62208: 2003
MIV 200	Mounting plate (Galvanized steel)					UL Canada
MIN 15	DIN-15 Mounting rail					Gost R
MIN 20	DIN-15 Mounting rail					
MIV 15	DIN-35 Mounting rail					
MIV 20	DIN-35 Mounting rail					
FP A 200/180	Front plate (Aluminium)					
HFP 180	Front plate hinge series					
FP 22046	Wall fastening lug (4 pcs)					

