




- Square solution
- 15.1mm x 15.1mm
- h=20.5 mm
- Material: ABS
- Temp. Range: -40/+65°C


All dimensions in mm

DIMENSIONS


(TH) + 16324



(TH w/LED) + 16325



(TH 2 w/LED) + 16326



NON-ILLUMINATED – HOW TO ORDER

Switch

1 5

+

Extender

1 6 2 7 0

+

Cap

1 6 3 0 0

+

Bezel

1 6 3 2 4

15501 mom. silver

15551 lat. silver

15502 mom. gold

15552 lat. gold

15500 silent silver

15401 mom. silver high temp.

15402 mom. gold high temp.

15420 silent gold high temp.

15451 lat. silver high temp.

15452 lat. gold high temp.



00 blue

01 brown

02 green

03 grey

04 yellow

05 golden

06 white



07 orange

08 red

09 black

30 ultra blue

40 dusty blue

42 aqua blue

32 mint green

33 tele grey

34 melon

38 noble red

50 metal dark blue

53 metal light grey

57 metal dark grey


58 metal bordeaux

01 brown

03 grey

06 white

09 black



ILLUMINATED – HOW TO ORDER

Switch

1 5

+

Extender

1 6 2 7 0

+

Cap

1 6 3 0 0

+

Bezel

1 6 3 2 4

+

Lens

1 6 3 2 7

+

LED

1 6 9 2 2



16325



16326



02 green

04 yellow

08 red

Lens 16327

2 required



02 green

04 yellow

08 red

LED 16922

2 required



Ordering example: 15551+16270+1630030+1632403 (non-illuminated) OR 15501+16270+1630008+1632509+1632708+1692208 (illuminated)

Please see colour codes, updates of products and changes of specifications on www.mec.dk