


Stereo Phone Jacks

161-3540, 161-3541

KOBI CONN

Stereo Phone Jacks



Dimensions: mm (In)

SPECIFICATIONS

Type:	Stereo Phone with Switch
Dielectric Strength:	250VAC for 1 Minute
Insulation Resistance:	100MΩ min. @ 250VDC
Contact Resistance:	30mΩ max.
Insertion/Extraction Force:	.3Kg ~2Kg
Life:	10,000 Cycles min.
Operating Temperature:	-10°C ~ +70°C
Body:	15% Glass Reinforced PBT
Cover:	Polycarbonate
Springs:	Stainless Steel
Barrel:	Nickel Plated Brass
Bushing:	161-3540 - Nickel Plated Brass; 161-3541 - 15% Glass Reinforced PBT
Terminals:	Silver Plated Phosphor Bronze

Date Last Revised: 10-15-05

Available from Mouser Electronics
1-800-346-6873
www.mouser.com

KC-300486

161-3540, 161-3541

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[161-3540](#) [161-3541](#)