



Copyright FCI.

D

A

B

C

5.82^{+0.23}₋₀

Ø3.8

6.17^{+0.24}₋₀

0.78^{+0.24}₋₀

CT PIN

CT SOCKET


16.79^{+0.25}₋₀

24.99^{±0.12}

8.23^{+0.23}₋₀

12.55^{±0.38}

LAYOUT DIMENSIONS (after plating)
CONNECTOR SIDE VIEW



REV F - 2006-04-17


1

2


3

4

10.71^{+0.53}₋₀



DETAIL OF PRESS FIT
Scale: 3



DEV2V2P93C5G40	UNC 4.40
DEV2V2P93C6G40	UNC 4.40
DEI2V2P93C5G40	M3
DEI2V2P93C6G40	M3
PART NUMBER	Threaded A

GENERAL CHARACTERISTICS : SEE DRAWING C01-8639-0002

European Views

www.fciconnect.com			surface ISO 1302	tolerance std ISO 406 ISO 1101	projection mm	size A3		Scale 2	
TOLERANCES UNLESS OTHERWISE SPECIFIED			ANGULAR	LINEAR	0.X	±0.1	0.XX	±0.1	0.XXX
Dr			PESSON	1997/05/06	0.XX	±0.1	0.XXX	±0.1	ECN
Eng			PESSON	1997/05/06	0.XX	±0.1	0.XXX	±0.1	LS06-0097
Chr			LEGARE	1997/05/06	0.XX	±0.1	0.XXX	±0.1	Spec ref
Appr			LEGARE	1997/05/06	0.XX	±0.1	0.XXX	±0.1	-
Product family			D-SUB			Rev.			
FCI			MALE CONNECTOR 2V2 with s			C01-8639-1527			G
title			power press fit			C01-8639-1527			G
catalog no			-			CUSTOMER			sheet 1 of 1

rev	ecn no	dr	date
D	-	BAR	2003/11/07
E	LS05-004	MPE	2005/02/08
F	LS05-0090	LGO	2005/10/12
G	LS06-0097	LGO	2006/07/29
-	-	-	-
-	-	-	-
-	-	-	-

PDM: Rev:G

STATUS Released

Printed: Oct 01, 2010