




NOTES:

- ALL DIMENSIONS IN MM [INCH]
- GENERAL TOLERANCE: $X.X \pm 0.4$
 $X.XX \pm 0.25$
- TERMINAL NUMBERS FOR REF. ONLY
- CONTACT RATING: 0.1A @ 30VDC
- TRAVEL: FULL = 2.5 ± 0.3
- OPERATING FORCE: 250 ± 100 gf
- ELECTRICAL LIFE: 10,000 CYCLES
- ▲ DENOTES CRITICAL PARAMETER
- CONTACT MATERIAL: SILVER
- CONTACT RESISTANCE: 50m OHM MAX.
- OPERATING TEMPERATURE: -20c TO +70c
- INSULATION RESISTANCE: 100M OHMS MIN.
- LED COLOR: BLUE
- 2002/95/EC (RoHS) COMPLIANT AND HALOGEN FREE



E-SWITCH™

TITLE TL22050ABPBB

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

B	19554	DIM CHANGES & UPDATE	12/30/10	BGL
A	18806	New-Release	1/20/10	rc
REV	PCR NO	DESCRIPTION	DATE	BY

SCALE 2:1

DATE 1/20/2010

DR rc

DWG B401013

REV B