




|                                       |                                                          |                                                        |                                                     |                                                        |                 |
|---------------------------------------|----------------------------------------------------------|--------------------------------------------------------|-----------------------------------------------------|--------------------------------------------------------|-----------------|
| <b>C-280357</b><br>NUMBER<br>OBSOLETE | ADATTO PER APPLIC. STANDARD<br>(FOR STANDARD APPLICATOR) |                                                        | ADATTO PER MINI APPLICATOR<br>(FOR MINI APPLICATOR) |                                                        |                 |
|                                       | N° PART.<br>(PART/NUMBER)                                | MATERIALE/FINITURA<br>(MATERIAL/FINISH)                | N° PART.<br>(PART/NUMBER)                           | MATERIALE/FINITURA<br>(MATERIAL/FINISH)                |                 |
|                                       | <del>280357-1</del>                                      | <del>BRONZO FOSFOROSO<br/>(PHOSPH. BRASS)</del>        | <del>280428-1</del>                                 | <del>BRONZO FOSFOROSO<br/>(PHOSPH. BRASS)</del>        | <b>OBSOLETE</b> |
|                                       | <del>280357-2</del>                                      | <del>BRONZO FOSF. STAGNATO<br/>(TIN PL. PH. BR.)</del> | <del>280428-2</del>                                 | <del>BRONZO FOSF. STAGNATO<br/>(TIN PL. PH. BR.)</del> |                 |
|                                       | <del>280357-3</del>                                      | <del>OTTONE<br/>(BRASS)</del>                          | <del>280428-3</del>                                 | <del>OTTONE<br/>(BRASS)</del>                          | <b>OBSOLETE</b> |
|                                       | <del>280357-4</del>                                      | <del>OTTONE STAGNATO<br/>(FIN PL. BRASS)</del>         | <del>280428-4</del>                                 | <del>OTTONE STAGNATO<br/>(FIN PL. BRASS)</del>         |                 |
|                                       |                                                          |                                                        | <del>280428-4</del>                                 | <del>OTTONE STAGNATO<br/>(TIN PL. BRASS)</del>         | <b>OBSOLETE</b> |

Adatto per linguetta di sp. 0.8  
(TO FIT 0.8 mm TAB THK)



Sez. A-A



© 1973 BY AMP INCORPORATED. ALL RIGHTS RESERVED. AMP PRODUCTS COVERED BY PATENTS AND/OR PATENTS PENDING.

CUSTOMER COPY  
REFERENCE ONLY

MATERIAL AND FINISH

VEDERE TABELLA  
(SEE TABLE)

**TE**

TE Connectivity

CLASS .250 SERIES

WIRE RANGE - INSULATION  
0.5 - 1.5 mm<sup>2</sup> | 3.3 Ø MAX

TYPE F. F.

TOLERANCE EXCEPT  
AS NOTED  
3 0.4

SCALE

4:1

LOC

I

NO

A

C-280357

REV

N2

NAME

.250 SERIES FLAG FASTEN-ON REC.

N2 REVISED PER ECR-17-013054

BDA

TD

22NOV2017

LTR

REVISION RECORD

DR

CHK

DATE

DR

9-1-73

BY

18/12/74

CHK

18/12/74

APP

DIMENSIONS IN MM. DO NOT SCALE PRINT

PRINT DIST