




AC Inlets

161-0707-1-E, 161-0707-1-187-E, 161-0707-1-250-E



AC Inlets



Dimensions: mm (in.)

SPECIFICATIONS	
Type:	screw mount, Class I, AC power
Rating:	15A / 250 VAC
Insulation resistance:	100M Ω @ 500VDC
Dielectric strength:	2000VAC for 1 minute
Temperature rating:	65°C
Housing:	PBT
Terminal:	tin plated copper alloy
RoHS Compliant	

Date Last Revised: 03/21/07

Available from Mouser Electronics
1-800-346-6873 / www.mouser.com

KC- 301141

Specifications are subject to change without notice. No liability or warranty implied by this information. Environmental compliance based on producer documentation.

161-0707-1-E, 161-0707-1-187-E, 161-0707-1-250-E

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[161-0707-1-187-E](#) [161-0707-1-250-E](#) [161-0707-1-E](#)