

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NUMBER	Min. Exp. I.D. [in. (mm)]	Max. Rec. ID [in. (mm)]	NOMINAL REC WALL THICKNESS [in. (mm)]
HSTTT03-48-0	.034 (0.9)	.015 (1.4)	.009±.002 (0.2±.05)
HSTTT04-48-0	.038 (1.0)	.018 (0.5)	.009±.002 (0.2±.05)
HSTTT046-48-0	.046 (1.2)	.022 (0.5)	.010±.002 (0.3±.05)
HSTTT05-48-0	.050 (1.3)	.027 (0.7)	.010±.002 (0.3±.05)
HSTTT055-48-0	.055 (1.4)	.032 (0.8)	.012±.003 (0.3±.08)
HSTTT06-48-0	.060 (1.5)	.039 (1.0)	.012±.003 (0.3±.08)
HSTTT08-48-0	.076 (1.9)	.049 (1.2)	.012±.003 (0.3±.08)
HSTTT09-48-0	.093 (2.3)	.061 (1.6)	.012±.003 (0.3±.08)
HSTTT12-48-0	.120 (3.0)	.072 (1.8)	.012±.003 (0.3±.08)
HSTTT15-48-0	.150 (3.8)	.089 (2.3)	.012±.003 (0.3±.08)
HSTTT19-48-0	.191 (4.9)	.112 (2.8)	.012±.003 (0.3±.08)
HSTTT24-48-0	.240 (6.0)	.141 (3.6)	.015±.004 (0.4±0.1)
HSTTT30-48-0	.302 (7.7)	.178 (4.5)	.015±.004 (0.4±0.1)
HSTTT37-48-0	.370 (9.4)	.224 (5.7)	.015±.004 (0.4±0.1)
HSTTT43-48-0	.430 (10.9)	.278 (7.0)	.015±.004 (0.4±0.1)
HSTTT47-48-0	.470 (11.9)	.347 (8.8)	.015±.004 (0.4±0.1)
HSTTT56-48-5*	.560 (14.2)	.399 (10.1)	.015±.003 (0.4±0.1)
HSTTT66-48-0*	.655 (16.6)	.462 (11.7)	.018±.004 (0.5±0.1)
HSTTT75-48-5*	.750 (19.0)	.524 (13.3)	.018±.004 (0.5±0.1)
HSTTT93-48-5*	.930 (23.6)	.655 (16.6)	.020±.004 (0.5±0.1)
HSTTT112-48-5*	1.125 (28.6)	.786 (20.0)	.025±.005 (0.6±.13)
HSTTT131-48-2*	1.310 (33.3)	.911 (23.1)	.030±.006 (0.8±.15)
HSTTT150-48-2*	1.500 (38.1)	1.036 (26.3)	.030±.006 (0.8±.15)



NOTES:



- APPROXIMATE SHRINK RATIO: 2:1
- MATERIAL: POLYTETRAFLUOROETHYLENE
- COLOR: WHITE TRANSLUCENT
- TEFLON IS A REGISTERED TRADEMARK OF E.I.DuPont.
- SHRINK RATIOS ARE APPROXIMATIONS; PLEASE REFER TO DIMENSIONAL TABLE FOR THE EXACT MINIMUM EXPANDED AND MAXIMUM RECOVERED I.D.'S
- "ALL WARRANTIES, INCLUDING MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE, ARE EXCLUDED. (USER IS RESPONSIBLE TO DETERMINE SUITABILITY OF PRODUCT FOR INTENDED USE.)"
- (*) EXPANDED ID IS PER MIL-DTL-23053/12 CLASS 2 DIMENSIONAL REQUIREMENTS

PANDUIT NUMBERING SYSTEM

HSTTT - 05 48 0

PACKAGE QUANTITY: 2 = 2 PCS
5 = 5 PCS
0 = 25 PCS

LENGTH: 48 = 48" (1219mm)

EXPANDED INSIDE DIAMETER
TUBING SIZE

TFE TEFLON THIN WALL HEAT SHRINK
TUBING, 2:1 SHRINK RATIO

DIMENSIONS IN BRACKETS ARE METRIC [mm]

CAD FILENAME/LAYERS

G00239KL_DC_HSTTT_01

PANDUIT

CORP.

TINLEY PARK, ILLINOIS

TFE - TEFLON THIN WALL
HEAT SHRINK (HSTTT)
(CUSTOMER DRAWING)

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) ±0.05 (1.3) (.XXX) ±0.010 (0.25)
(.XX) ±0.02 (0.5) ANGLES ± 5°

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

OI	8/24/10	LEF	VJS	B ADDED APPROXIMATE TO NOTES LINE 1 A CHANGE 131 & 150 FROM +/- .005 TO +/- .006	GB0239KL	OI	RAMI		
R	5/13/03	LGG		INITIAL RELEASE	GB0239KL	R			
REV	DATE	BY	CHK	DESCRIPTION	ECN	-	R	CUST	SUP

DRAWN BY
LGRAVITT

MAT'L:

SCALE NONE

DATE
5/13/03

SEE NOTES

DRAWING NO.

GB0239KL

DWG
A
SIZE