




SANDVIK BELZER

Diagonal cutters

Produced by high performance ball-bearing steel, numerically controlled machine grinding guarantees edge angle accuracy and contact which increases tool reliability and consistency. Precision induction hardened edges, 63-65 HRC.
Handles with return spring.

Oval head



2646M - 2649



Product code	EAN code 731415+		A mm	B mm	C mm	D mm	F mm	Capacity mm	Bevel	
2646M	1487928	1	108	8	8	5	0,8	0,1-0,8	Ultra	44
2646R	1304706	1	110	10	10	6	0,8	0,2-1,25	Micro	46
2646RK *	1496678	1	110	10	10	6	0,8	0,2-1,25	Micro	46
2646RA	1834838	1	110	10	10	6	0,8	0,1-1,0	Ultra	46
2666	0058006	1	112,5	12,5	12,5	6	1,2	0,3-1,6	Micro	50
2649	0058013	1	125	16	16	8	1,6	0,4-2,0	Micro	88

Tapered head

2646 - 2648A



Product code	EAN code 731415+		A mm	B mm	C mm	D mm	F mm	Capacity mm	Bevel	
2646	1304638	1	110	10	10	6	0,8	0,2-1,25	Micro	46
2646K *	1495862	1	110	10	10	6	0,8	0,2-1,25	Micro	46
2646A	1304645	1	110	10	10	6	0,8	0,1-1,0	Ultra	46
2646AK *	1396619	1	110	10	10	6	0,8	0,1-1,0	Ultra	46
2666FK	1066079	1	112,5	12,5	12,5	6	1,2	0,2-1,25	Ultra	49
2666FKK *	1496593	1	112,5	12,5	12,5	6	1,2	0,2-1,25	Ultra	49
2648 *	1304713	1	125	16	16	8	1,6	0,4-2,0	Micro	88
2648A	1304720	1	125	16	16	8	1,6	0,3-1,6	Ultra	88

* with leadcatcher