



Part No	MPM PRT No	DESCRIPTION
1212020001	C22200N0R	TYPE B IND BLACK NBR GASKET
1212020002	C22200N0RCN	TYPE B IND BLACK NBR GASKET BULK
1212020003	C22200N0S	TYPE B IND BLACK SILICONE GASKET
1212020004	C22200G0R	TYPE B IND GRAY NBR GASKET
1212020005	C22200G0S	TYPE B IND GRAY SILICONE GASKET
1212020006	C22200T0R	TYPE B IND TRANSPARENT NBR GASKET
1212020007	C22200T0S	TYPE B IND TRANSPARENT SILICONE GASKET
1212020008	C22200T2RSN	TYPE B IND TRANSPARENT NBR GASKET H12 BULK MOUNTED
1212020010	C22200W0RCNSA	TYPE B IND BLACK UL V0 NBR GASKET BULK
1212020011	C22200W0RSA	TYPE B IND BLACK UL V0 NBR GASKET
1212020012	C22200N2RSN	TYPE B IND BLACK NBR GASKET H12 BULK MOUNTED
1212020013	C22200W0SSA	TYPE B IND BLACK UL V0 SILICONE GASKET
1212020014	C22200W0SCNSA	TYPE B IND BLACK UL V0 SILICONE GASKET BULK
1212020015	C22200N6RSN	TYPE B IND BLACK NBR GASKET H6 BULK MOUNTED
1212020016	C22200N2GSN	TYPE B IND BLACK NO GASKET H12 BULK MOUNTED
1212020017	C22200W2RSNSA	TYPE B IND BLACK UL V0 NBR GASKET BULK MOUNTED
1212020018	C22200N2GCF	TYPE B IND BLACK NO GASKET H12 BULK FULLY MOUNTED
1212020019	C22200N0SCN	TYPE B IND BLACK SILICONE GASKET BULK



NOTES:

1. FOR SPECIFIC PART NUMBERS PLEASE CONTACT SALES OR CONSULT THE INTELLIGENT PART NUMBERS IN THE TABLE ATTACHED
2. PACKAGING SPECIFICATION: PLEASE SEE PK-121201-001
3. PRODUCT SPECIFICATION: PLEASE SEE PS-121201-001, WITH EXCEPTION.
4. CABLE SIZES 4 - 9 MM DIAMETER
5. TIGHTENING TORQUES: SEE PS-121201-001
6. GROUND POSITION SHOWN H12

LAST INSPECTION NUMBER 8



ITEM	DESCRIPTION
1	31mm M3 SCREW WITH GASKET
2	TYPE B COVER
3	TYPE B IND INSERT
4	TYPE B GASKET
5	GROMMET
6	EXTERNAL NUT

C22200N0R****

SERIES _____
C22= EXTERNAL THREAD FORM B INDUSTRIAL
POLES _____
2= 2 POLE
THREAD _____
00 = EXTERNAL THREAD
MATERIAL AND HOUSING COLOR _____
G= PA6 GRAY, N= PA6 BLACK, W= PA6 BLACK V0, T= TRANSPARENT
GROUND POSITION _____
0= UNMOUNTED, 2= H12 & 6 =H6
SCREW AND GASKET _____
R= INTEGRATED NBR GASKET AND IP67 SCREW
S= INTEGRATED SILICON GASKET AND IP67 SCREW
G= IP67 SCREW, NO GASKET
NON STANDARD PACKAGING _____
CN= BULK PACK UN-MOUNTED
SN= BULK PACK MOUNTED
67= NEUTRAL PACKAGING
CF= BULK PACK FULLY MOUNTED
ADDITIONAL CODES _____
SA= UL AGENCY APPROVAL

UPDATED NOTE 3. EC NO: IPG2015-1871 DRWN:BCAFFREY 2015/04/27 CHKD: APPR:STGR/FF/IN 2015/05/13		QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED) <table border="1"> <tr> <th></th> <th>mm</th> <th>INCH</th> </tr> <tr> <td>4 PLACES</td> <td>±---</td> <td>±---</td> </tr> <tr> <td>3 PLACES</td> <td>±---</td> <td>±---</td> </tr> <tr> <td>2 PLACES</td> <td>±0.10</td> <td>±---</td> </tr> <tr> <td>1 PLACE</td> <td>±0.20</td> <td>±---</td> </tr> </table> ANGULAR ± 2 ° DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		mm	INCH	4 PLACES	±---	±---	3 PLACES	±---	±---	2 PLACES	±0.10	±---	1 PLACE	±0.20	±---	DIMENSION STYLE MM ONLY DRAWN BY: D MAHER DATE: 2009/3/24 CHECKED BY: S MCGREEVY DATE: 2009/3/24 APPROVED BY: EFOLAN DATE: 2010/10/18 MATERIAL NO.	SCALE: 1:1 DESIGN UNITS: METRIC TITLE: EXTERNAL THREAD C22 SERIES 121202 MOLEX INCORPORATED DOCUMENT NO. SD-121202-001 SHEET NO. 1 OF 1	EM-121202-002 THIRD ANGLE PROJECTION
	mm	INCH																			
4 PLACES	±---	±---																			
3 PLACES	±---	±---																			
2 PLACES	±0.10	±---																			
1 PLACE	±0.20	±---																			

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION