

06.63.206



Detailed View



06.63.206 **Locking Support, Threaded Female**

Length	20,0 mm
Material	Nylon 66
Thread Typ	M3
Dia. Hole Board	4,0 mm
Dia. Hole Chassis	3,2 mm
Typ	Support Threaded Male
UL-Flamability	UL94 HB
Board Thickness	2,10 mm
Model	Support Treaded Female
Colour	black
Design	Screw Mounting
	RoHS konform / WEEE konform / 76/769/EWG konform / PAKs frei

Locking Su



Length
Material
Thread Typ

20,0 mm
Nylon 66
M3

Dia. Hole Board	4,0 mm
Dia. Hole Chassis	3,2 mm
Typ	Support Thread
UL-Flamability	UL94 HB
Board Thickness	2,10 mm
Model	Support Tread
Colour	black
Design	Screw Mounting
	RoHS konform
Specifications	Details...

Deliverydate	from stock
Price Grading	100 to 499 piece
	500 to 999 piece
	1000 to 2499 pi
	more than 2500

To order

