


PVC insulated Flexible cable



Technical & Specification

Cross-section	0.25mm ²
External Dia.	ø1.4mm ±0.1
Construction	50 x ø0.08mm
Material:	
Conductor	Cu blank
Insulator	PVC
Jacket Color	Black/White/Blue/ Red/Grey/Orange/ Green/Yellow/Violett/ Yellow+Green
Dielectric strength	1kv/ 1 minute
Rated voltage	<75VDC / 50VAC
Conductor Resistance	72.5Ω/KM at 20°C
Insulator Resistance	15MΩ/KM at 20°C
Flame Class	94V-2
Operating Temperature	-10 ~ 70°C