


## Crocodile clips



## AGF 2

CE

Product	AGF 2
description	Extra-fine alligator clip, particularly suited for gripping densely packed extremely small contact points. Contact tongues insulated on the outside to prevent short circuits. Plug connection through 2 mm and 4 mm diameter connectors.
operating instruction	BA420
article-no. / *colour	9312721xx  <div style="display: flex; justify-content: space-around; align-items: center;"> <span>00</span> <span>black</span> <span>01</span> <span>red</span> </div>
drawing	
technical data	
connection	unsprung socket 4 mm
rated voltage <sup>(1)</sup>	30 VAC / 60 VDC
measurement cat. acc. to IEC 61010	O <sup>(3)</sup>
rated current <sup>(1)</sup> (consider derating curve)	6 A
material socket	brass, nickel plated
housing material	PVC-P
temperature range acc. To IEC61010 <sup>(2)</sup>	-25 °C to +80 °C
clamping range	4 mm
standard	IEC 61010

<sup>(1)</sup> for normal environmental conditions -5°C to +40°C

<sup>(2)</sup> contact the manufacturer for applications at deviating temperature ranges

(3) without rated measurement category, for other circuits that are not directly connected to mains stand: 19.06.2019