









Contact arrangement / view from termination side




Contact arrangement / view from termination side



Contact arrangement / view from termination side



Contact arrangement / view from termination side




NOTES:


- 1 SUITABLE CRIMP CONTACTS: SERIES HE/HA
OUTER DIMENSIONS OF INSULATION: MAX. Ø3,2 MM
 - 2 SUITABLE HOOD SIZE 5; 7; 9; 11: SERIES HA; HD
SUITABLE INSERTION AND EXTRACTION TOOL:
SCREWDRIVER 0,5x3 DIN 5264
 - 3 Strip lenght: Screw conection 10mm
Spring clamp conection 10mm Crimp conection 7.5mm
 - 4 STANDARDS:
DIN EN 61984; DIN EN 60664-1
 - 5 PACKAGING:
5 SETS IN A CARTON, PRE-MOUNTED
 - 6 SPECIAL PACKAGING: Krauss-Maffei
PACKAGING UNIT: 300 PIECES
 - 7 SPECIAL PACKAGING: Krauss-Maffei
PACKAGING UNIT: 150 PIECES
 - 8 SPECIAL PACKAGING: AIS
PACKAGING UNIT: 250 PIECES
 - 9 SPECIAL PACKAGING: WIELAND
PACKAGING UNIT: 100 PIECES
-  SEE TE CONNECTIVITY QUALITYMANAGEMENT PROC

Panel cut-out for contact insert

when used without housing



Assembling instruction



 DISTANCE FOR SAFETY
CONTACT MARKING MAX. 24 mm

[illegible]