





REV.	DATE	DESCRIPTION
NC	03/27/05	INITIAL RELEASE



RECOMMENDED
CABLE STRIPPING DIM'S



NOTE:

1. CRIMPED FERRULE
HEX CRIMP SIZE .429"
2. CRIMPED CONTACT PIN
HEX CRIMP SIZE .118"

					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 - 8mm ± 0.20mm 8 - 30mm ± 0.40mm 30 - 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 - .315 = ± 0.007" .315 - 1.180 = ± 0.015" 1.180 - 4.724 = ± 0.020"	APPROVALS	DATE	Amphenol Connex					
8						DRAWN	G.R.S.						03/27/05
7						CHECKED			PART DESCRIPTION SMA CRIMP PLUG (FOR RG-8/U, 213/U CABLE)				
6						ISSUED							
5						SHEET	1 OF 1		PART NO. 132368				
4	FERRULE	COPPER	GOLD	1									
3	CONTACT PIN	BRASS	GOLD	1					DWG NO. 132368.DWG				
2	INSULATOR	TEFLON	NATURAL	1									
1	BODY	BRASS	GOLD	1					REV. A	SIZE A	SCALE NA		
	DESCRIPTION	MATERIAL	FINISH	QTY	DO NOT SCALE DRAWING	CAD FILE	C:/132/132368.DWG						