



NOTES:

1. MATERIAL:  
BODY - BRONZE (GUN METAL)  
SCREW - STEEL, ZINC PLATED
2. PARTS ARE cULus LISTED TO UL467 AS  
GROUNDING & BONDING EQUIPMENT.
3. SEE WWW.PANDUIT.COM FOR PART NUMBER  
SUFFIX DESIGNATION FOR PACKAGE SIZE.



| PART NUMBER    | CONDUIT HUB SIZE | DIMENSIONS IN [mm] ±.05 [1.3] |                 |                | DESCRIPTION                                                 | WATER PIPE     | GROUNDING WIRE |
|----------------|------------------|-------------------------------|-----------------|----------------|-------------------------------------------------------------|----------------|----------------|
|                |                  | B                             | C               | D              |                                                             |                |                |
| GPC 4 - 1 - 12 | 1/2 "            | 1.65<br>[41.9]                | 1.00<br>[25.4]  | 0.56<br>[14.2] | GROUND CLAMP FOR RIGID<br>CONDUIT WITH 1/2 HUB              | 1/2 " - 1"     | 8 - 4 STR      |
| GPC 4 - 1 - 34 | 3/4 "            | 1.65<br>[41.9]                | 1.00<br>[25.4]  | 0.56<br>[14.2] | GROUND CLAMP FOR RIGID<br>CONDUIT WITH STEEL SCREWS 3/4 HUB | 1/2 " - 1"     | 8 - 4 STR      |
| GPC 4 - 1 - 1  | 1"               | 1.65<br>[41.9]                | 1.00<br>[25.4]  | 0.56<br>[14.2] | GROUND CLAMP FOR RIGID<br>CONDUIT WITH STEEL SCREWS 1 HUB   | 1/2 " - 1"     | 8 - 4 STR      |
| GPC 4 - 2 - 12 | 1/2 "            | 2.22<br>[56.4]                | 2.08<br>[52.8]  | 1.33<br>[33.8] | GROUND CLAMP FOR RIGID<br>CONDUIT WITH 1/2 HUB              | 1-1/4 " - 2"   | 8 - 4 STR      |
| GPC 4 - 2 - 34 | 3/4 "            | 2.22<br>[56.4]                | 2.08<br>[52.8]  | 1.33<br>[33.8] | GROUND CLAMP FOR RIGID<br>CONDUIT WITH STEEL SCREWS 3/4 HUB | 1-1/4 " - 2"   | 8 - 4 STR      |
| GPC 4 - 2 - 1  | 1"               | 2.22<br>[56.4]                | 2.08<br>[52.8]  | 1.33<br>[33.8] | GROUND CLAMP FOR RIGID<br>CONDUIT WITH STEEL SCREWS 1 HUB   | 1-1/4 " - 2"   | 8 - 4 STR      |
| GPC 4 - 4 - 12 | 1/2 "            | 4.25<br>[108.0]               | 3.81<br>[96.8]  | 2.75<br>[69.9] | GROUND CLAMP FOR RIGID<br>CONDUIT WITH 1/2 HUB              | 2 - 1/2 " - 4" | 8 - 4 STR      |
| GPC 4 - 4 - 34 | 3/4 "            | 4.25<br>[108.0]               | 3.81<br>[96.8]  | 2.75<br>[69.9] | GROUND CLAMP FOR RIGID<br>CONDUIT WITH 3/4 HUB              | 2 - 1/2 " - 4" | 8 - 4 STR      |
| GPC 4 - 4 - 1  | 1"               | 4.25<br>[108.0]               | 3.81<br>[96.8]  | 2.75<br>[69.9] | GROUND CLAMP FOR RIGID<br>CONDUIT WITH 1 HUB                | 2 - 1/2 " - 4" | 8 - 4 STR      |
| GPC 4 - 6 - 12 | 1/2 "            | 5.20<br>[132.1]               | 6.00<br>[152.4] | 2.90<br>[73.7] | GROUND CLAMP FOR RIGID<br>CONDUIT WITH 1/2 HUB              | 4 - 1/2 " - 6" | 8 - 4 STR      |
| GPC 4 - 6 - 34 | 3/4 "            | 5.20<br>[132.1]               | 6.00<br>[152.4] | 2.90<br>[73.7] | GROUND CLAMP FOR RIGID<br>CONDUIT WITH 1/2 HUB              | 4 - 1/2 " - 6" | 8 - 4 STR      |
| GPC 4 - 6 - 1  | 1"               | 5.20<br>[132.1]               | 6.00<br>[152.4] | 2.90<br>[73.7] | GROUND CLAMP FOR RIGID<br>CONDUIT WITH STEEL SCREWS 1 HUB   | 4 - 1/2 " - 6" | 8 - 4 STR      |

|     |      |      |      |     |                                                                                                                                                                                                                                                                                                                    |             |                                                                    |  |                       |  |
|-----|------|------|------|-----|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------|--------------------------------------------------------------------|--|-----------------------|--|
|     |      |      |      |     |                                                                                                                                                                                                                                                                                                                    |             | TITLE                                                              |  |                       |  |
|     |      |      |      |     |                                                                                                                                                                                                                                                                                                                    |             | BRONZE GROUND PIPE CLAMP<br>CUSTOMER DRAWING                       |  |                       |  |
|     |      |      |      |     |                                                                                                                                                                                                                                                                                                                    |             | ITEM REVISION NAME                                                 |  | 10J018AK/01           |  |
|     |      |      |      |     |                                                                                                                                                                                                                                                                                                                    |             | DATASET FILE NAME                                                  |  | 10J018AK-JC/01.SLDDRW |  |
| 01  | 8/12 | JHNU | SRBI | RGB | REVISED P/N'S: GPC4-1-12 WAS GPC6-1-12, GPC4-1-34 WAS GPC6-1-34, GPC4-1-1 WAS GPC6-1-1, GPC4-2-12 WAS GPC6-2-12, GPC4-2-34 WAS GPC6-2-34, GPC4-2-1 WAS GPC6-2-1, GPC4-4-12 WAS GPC6-4-12, GPC4-4-34 WAS GPC6-4-34, GPC4-4-1 WAS GPC 6-4-1, GPC4-6-12 WAS GPC6-6-12, GPC4-6-34 WAS GPC6-6-34, GPC4-6-1 WAS GPC6-6-1 | 10J018AK-JC | UNLESS OTHERWISE SPECIFIED,<br>DIMENSIONAL TOLERANCES ARE: IN [mm] |  | MATERIAL              |  |
| 00  | 7/12 | JHNU | SRBI | RGB | DRAWING RELEASED                                                                                                                                                                                                                                                                                                   | 10J018AK-JC | .XXX ±<br>.XX ±<br>ANGLES ±                                        |  | SEE NOTES             |  |
| REV | DATE | BY   | CHK  | APR | DESCRIPTION                                                                                                                                                                                                                                                                                                        | ECN         | THIRD ANGLE<br>PROJECTION                                          |  | DRAWING NUMBER        |  |
|     |      |      |      |     |                                                                                                                                                                                                                                                                                                                    |             | DRAWN BY                                                           |  | 10J018AK-JC           |  |
|     |      |      |      |     |                                                                                                                                                                                                                                                                                                                    |             | DATE                                                               |  | SHEET 1 OF 1          |  |
|     |      |      |      |     |                                                                                                                                                                                                                                                                                                                    |             | CHK                                                                |  | SIZE                  |  |
|     |      |      |      |     |                                                                                                                                                                                                                                                                                                                    |             | SCALE                                                              |  | B                     |  |
|     |      |      |      |     |                                                                                                                                                                                                                                                                                                                    |             | N/A                                                                |  |                       |  |