


| LOC | DIST | REVISIONS |     |                           |           |     |      |
|-----|------|-----------|-----|---------------------------|-----------|-----|------|
|     |      | P         | LTR | DESCRIPTION               | DATE      | DWN | APVD |
| G   | 14   |           | K2  | REVISED PER ECO-13-008373 | 20MAY2013 | KH  | DR   |



**AMP**  
WIRE RANGE

12-10 AWG  
SOLID OR STRANDED

- 1 STAMP AMP 12-10, APPROX AS SHOWN
- 2 WIRE BARREL COLOR CODED ORANGE TO DENOTE NICKEL MATERIAL
- 3 NICKEL PER ASTM B-162, ANNEALED
- 4 NOTE DELETED.

|      |                   |            |
|------|-------------------|------------|
| 50   | LOOSE PIECE , BOX | 8-323745-2 |
| 2500 | 323745 ON TAPE    | 2-323745-6 |
| --   | LOOSE PIECE       | 323745     |
| QTY  | PACKAGE TYPE      | PART NO.   |

MAX RECOMMENDED OPERATING TEMPERATURE:  
649°C[1200° F]

VOLTAGE RATING:  
N/A

CIRCULAR MIL AREA:  
2.62-6.64mm²[5,180-13,100]  
SOLID OR STRANDED

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:  
mm [INCHES]

MATERIAL

TOLERANCES UNLESS OTHERWISE SPECIFIED:  
0 PLC ± -  
1 PLC ± -  
2 PLC ± -  
3 PLC ± -  
4 PLC ± -  
ANGLES ± -  
FINISH -

DWN  
JR RUTH  
CHK  
T MICHELUTTI  
APVD  
T MICHELUTTI  
PRODUCT SPEC  
APPLICATION SPEC  
WEIGHT -

CUSTOMER DRAWING

SCALE 10:1

SHEET 1 OF 1

REV K2

TE Connectivity

NAME  
TERMINAL, RING TONGUE,  
HIGH TEMPERATURE,  
STRATO-THERM

SIZE  
A2

CAGE CODE  
00779

DRAWING NO  
C-323745

RESTRICTED TO  
-

1471-9 (3/11)