

LED-Leuchten für Schalttafel-Einbau Ø 16 / 16,5 mm

Serie SKCD 16

DC-Ausführung mit zusätzlicher Schutzdiode in bewährtem Isolierkörper mit aufgeschweißter Kunststoffblende. Das metalisierte Gehäuse ist Aluminium-bedampft und mit einer resistenten Schutzlackierung versehen.

Stromaufnahme

- bei Nennspannung ca. 14 mA

Serie SKCC und SKCE 16

Multi-Funktions Meldeleuchte. Gehäuseausführung wie SKCD 16. Ausführung für 2-Farb Betrieb klar-transparente Blende.

Ausführungen

- 1-farbige Anzeige mit Blink- und statischer Funktion
- 3-Farben-Anzeige, statisch
- Kombi-Leuchte mit rotem Blink- und grünem Dauerlicht, Mischfarbenansteuerung (orange) über getrennten Anodeneingang z.B. zur Signalisation der Funktion "Lampenprüfung"

Stromaufnahme

bei Nennspannung 12/24 V
rot ca. 12 mA
grün ca. 18 mA
Mischfarbe ca. 30 mA

Gültig für beide Typen

Einbau-Öffnung

Bohrung Ø 16+0,5 mm

Anschluß

Flachstecker 2,8x0,5 mm



Optionen

- Für IP-67 Ausführung nur Außen-O-Ring erforderlich, siehe Seite 34
- Litzen-Anschluß 0,5 mm, siehe Seite 34
- Blende in klar-transparent



LED- und Material-Daten

siehe Info-Seite

SKCD 16




SKCE/SKCC 16



Pinning SKCE/SKCC

AR Anode rot/red
AG Anode grün/green
AM Mischfarbe/Mixed colour
K Kathode



LED indicators for board installation mounting-Ø 16 / 16,5 mm

Series SKCD

DC-version with additional protective diode in insulated body with flash-welded lens. Housing aluminium-plated and with durable protective lacquer coating.

Power Consumption

- at rated voltage approx. 14mA

Series SKCC and SKCE 16

Multi-function indicator, housing like SKCD 16. Type for 2-coloured operation clear-transparent lens.

Types

- 1-coloured indicator with flashing and continuous function
- 3-coloured indicator, continuous combi-indicator with red flashing and green continuous light, mixed colour control (orange) by a separate anode input, f.ex. for signalisation of the function "lamp test".

Power Consumption

at rated voltage 12/24 V
red approx. 12mA
green approx. 18mA
mixed colour approx. 30mA

Valid for both types

Mounting-Ø 16+0,5 mm

Connections

tab terminals 2,8x0,5 mm

Options

- For IP 67 type only outside O-ring necessary, see page 34
- Stranded wire leads 0,5 mm, see page 34
- clear-transparent lens

LED-and material data

see info-page

Artikel-Nr.**Part-No.**[illegible]