

PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION

**Part Number:** [35151-0410](#)  
**Status:** **Active**  
**Overview:** [VersaBlade™ Wire-to-Wire Connector System](#)  
**Description:** Wire-to-Wire VersaBlade™ Hybrid Receptacle Housing, 4 Circuits, Polyester UL94V-0, Natural

**Documents:**  
[3D Model](#)  
[Drawing \(PDF\)](#)  
[Packaging Specification PK-35151-005 \(PDF\)](#)  
[RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

|     |           |
|-----|-----------|
| CSA | LR19980   |
| TUV | R72090206 |
| UL  | E29179    |

**General**

|                |                                                           |
|----------------|-----------------------------------------------------------|
| Product Family | Crimp Housings                                            |
| Series         | <a href="#">35151</a>                                     |
| Application    | Power, Wire-to-Wire                                       |
| Comments       | Polarized to Mating Part, Positive Lock                   |
| Overview       | <a href="#">VersaBlade™ Wire-to-Wire Connector System</a> |
| Product Name   | VersaBlade™                                               |
| UPC            | 800753876828                                              |


**Physical**

|                               |                 |
|-------------------------------|-----------------|
| Circuits (maximum)            | 4               |
| Color - Resin                 | Natural         |
| Flammability                  | 94V-0           |
| Gender                        | Female          |
| Glow-Wire Compliant           | No              |
| Keying to Mating Part         | None            |
| Lock to Mating Part           | Yes             |
| Material - Resin              | Polyester       |
| Net Weight                    | 3.653/g         |
| Number of Rows                | 2               |
| Packaging Type                | Bag             |
| Panel Mount                   | No              |
| Pitch - Mating Interface      | 8.90mm          |
| Polarized to Mating Part      | Yes             |
| Stackable                     | No              |
| Temperature Range - Operating | -40°C to +120°C |

**Material Info**

**Reference - Drawing Numbers**

|                         |               |
|-------------------------|---------------|
| Packaging Specification | PK-35151-005  |
| Sales Drawing           | SD-35151-0410 |



Series

image - Reference only

**EU RoHS**  
**ELV and RoHS**  
**Compliant**  
**REACH SVHC**  
**Contains SVHC: No**  
**Low-Halogen Status**  
**Not Low-Halogen**

**China RoHS**



**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

**Search Parts in this Series**  
[35151Series](#)

**Mates With**  
[35150](#) Plug Housing

**Use With**  
VersaBlade™ Crimp Terminals [35745](#) ,  
[35746](#) , [35747](#)