






Dimensions: mm (In.)

**Mechanical Specifications:**

- Mechanical Life: 40,000 make-and-break cycles
- Operating Temperature: -30°C to 85°C

Electrical Specifications:

- Rating: 2A / 250VAC, 5A / 120 VAC or 28 VDC
- Contact Resistance: 10mΩ max. initial @ 2-4VDC 100mA
- Insulation Resistance: 1,000MΩ min.
- Dielectric Strength: 1,000 V RMS@sea level

Materials:

- Case: Diallyl phthalate (DAP)
- Actuator: Brass, chrome plated
- Bushing: Brass, nickel plated
- Housing: Stainless Steel
- Terminal/Contact: Silver or gold plated

Note:

- RoHS Compliant by Exemption

Mouser Stock No.	Type	Circuit
108-0017-EVX	DPDT	On-On
108-0018-EVX	DPDT	On-Off-On
108-0019-EVX	DPDT	On-(On)

Miniature Toggle Switches
108-0017-EVX, 108-0018-EVX, 108-0019-EVX

Mountain
Switch

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mountain Switch:

[108-0017-EVX](#) [108-0018-EVX](#) [108-0019-EVX](#)