



62781-2 Product Details

[Share](#) [Print](#) [Email](#)[Feedback](#) Active
 View 3D PDF

MAG-MATE Terminals

TERM MAG-MATE MINI 42-52 TPBR

62781-2 

TE Internal Number: 62781-2

Product Highlights [View All](#)

- Contact
- Special Cavity Size
- Terminal Line = Mini MAG-MATE
- Terminal Configuration = Poke-In
- Brass Material

[Pricing & Availability](#)[Request Sample](#)[Add to My Part List](#)[Buy Product through Distributor](#)[Documents](#)[Features](#)[Compliance](#)

Please Note:

Use the Product Drawing for all design activity

Product Type Features

Product Type	Contact
Terminal Line 	Mini MAG-MATE
Terminal Configuration 	Poke-In

Industry Standards

RoHS/ELV Compliance 	RoHS compliant, ELV compliant
Lead Free Solder Processes 	Not relevant for lead free process
RoHS/ELV Compliance History	Always was RoHS compliant

Dimensions

Terminal Height (mm [in]) 	8.76 [0.345]
---	--------------

Packaging Features

Packaging Method	Reel/Carton
------------------	-------------

Body Features

Cavity Size 	Special
Material 	Brass
Magnet Wire Range (mm [AWG]) 	0.02 - 0.06 [42 - 52]
Lead Wire Range (mm ² [AWG]) 	0.30 - 0.80 [18 - 22]
Plating Material 	Tin

Other

Brand	AMP
Comment	Solid or overcoated stranded lead wire only.; Splice Free

Related Products

Not quite the product you're looking for?

[Find Similar Products](#)[View Part in Product Feature Selector](#)[Check for Tooling](#)

Corporate Information

[About TE](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)
[Terms & Conditions](#)
[Privacy Policy](#)
[Global Accessibility Statement](#)

Quick Links

[Distributor Inventory](#)
[Product Cross Reference](#)
[Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

Customer Support

[Email or Chat With Us](#)
[Find a Phone Number](#)
[Knowledge Base](#)
[Manage Your Account](#)

Keep Me Informed

