

## Specifications:

|                         |                                    |
|-------------------------|------------------------------------|
| Sound level Category    | Medium Sound Level                 |
| Mode of Operation       | Slow Pulse                         |
| Mounting                | Panel (see note B)                 |
| Voltage Rating          | 30 to 120 Vac/dc                   |
| Frequency               | 1900 Hz $\pm$ 300 Hz               |
| Loudness (Min. Voltage) | 60 dB(A) min. @ 2 FT and 30 Vac/dc |
| Loudness (Max Voltage)  | 75 dB(A) min. @ 2FT and 120 Vac/dc |
| Current Draw            | 6 mA Max @ 30 Vac/dc               |
| Current Draw            | 20 mA Max @ 120 Vac/dc             |
| Min. Pulse Rate (PPS)   | 0.5 @ 30 Vac/dc                    |
| Max. Pulse Rate (PPS)   | 2.0 @ 120 Vac/dc                   |
| Duty Cycle (%)          | 50 (Approx)                        |
| Storage Temperature     | -40°C to +85°C                     |
| Operating Temperature   | -30°C to +65°C                     |
| Weight (Typical)        | 2.7 oz (76 g)                      |
| Housing                 | 6/6 Nylon, Color Black             |
| Options                 | For other options contact factory  |

Dimensions: Inches (mm)

UL Recognized 

RoHS Compliant

PART DIMENSIONS BEFORE CODE DATE 0809 5 PART DIMENSIONS AFTER CODE DATE 0810 1

