

2 / 4 Port - USB-PS/2 Combo KVMs



Features

1. Console your Keyboard/Mouse via either way of PS/2 and/or USB arbitrarily.
2. Complex connections with PCs via either way of PS/2 and/or USB arbitrarily.
3. Controls 2 / 4 computers from a single console (Keyboard/Mouse) over PS/2 and/or USB connections.
4. Supports Windows, Linux, Mac OS9/OSX, Sun Microsystems.
5. Emulates a keyboard on each PC to allow your computers to boot normally - without a keyboard error.
6. Supports hot-swap. All devices connected to the KVM can be added or removed at any time, without shutting the unit down.
7. Supports 2 types of switching:
 - (1) Hardware Push Button
 - (2) Hot-Keys on PS/2 and/or USB of keyboard arbitrarily.
8. Supports Auto-Scan function to alternate video between computers in preset intervals.
9. Supports LED display for PC status monitoring.
10. Supports VGA resolutions up to 2048 x 1536 @ 85HZ.
11. Supports Beeper during switching enabled.
12. Self powered through PS/2 and/or USB connection.
13. Fully compliant with the USB 1.1/ 2.0 specification.
14. Audio support IN / OUT (only audio version)
15. Incl. two 1,8 m KVM cable sets (HDDB15/M ⇔ HDDB15/M, 2xMiniDIN6/M, 1xUSB-A/M; audio version additional with two cable 2x3,5mm stereo/M ⇔ 2x3,5mm stereo/M)

System Requirements

Console

- A VGA, SVGA, Multisync monitor capable of the highest resolution.
- PS/2 and/or USB Keyboard/Mouse

Computer or Server

The following equipment must be equipped with each computer or server.

- A VGA, SVGA or Multisync card.
- Type A USB port and/or PS/2 6 pin mini-DIN for Keyboard and Mouse.

Specification

Number Of Computers Controlled		2 / 4
Selection Method		Push Button and Hot-Key (PS/2 and/or USB Keyboard)
LEDs		Red for PC Selection Green for PC On-Line ready
PC Connectors	Video	2 / 4 x HDB -15 female
		(USB & PS/2 signal combined)
	Speaker	2 / 4 audio female jacket (only audio version)
	Microphone	2 / 4 audio female jacket (only audio version)
Console Ports	Keyboard	1 x 6 pin PS/2 mini-DIN female
		1 x USB A type female (only USB –PS/2 version)
	Mouse	1 x 6 pin PS/2 mini-DIN female
		1 x USB A type female (only USB –PS/2 version)
	Video	1 x HDB -15 female
	Speaker	1 x audio female jacket (only audio version)
	Microphone	1 x audio female jacket (only audio version)
Auto-Scan Interval		From 5 to 250 Seconds
DDC, DDC2 monitor		Yes (Max. Resolution: 2048x1536) @ 85Hz
Hot Swappable		Yes
Operating systems supported		Windows 98SE/ME/2000/XP/2003 Server, Linux
		Mac OS9/OSX and Sun Micro System
Device driver		No Need
Power		By PS/2 and/or USB or External Power Adaptor (Optional)
Dimensions (L X W X H)		2-Port : 14.0 x 8.5 x 4.5 cm (5.5 x 3.3 x 1.7 inches)
		4-Port : 21.5 x 8.8 x 4.5 cm (8.5 x 3.4 x 1.7 inches)
Unit Weight		2-Port : ~ 450 g
		4-Port : ~ 650 g
Housing material		Metal
Operating Temperature		32~ 122°F (0~ 50°C)
Humidity		0%~80%RH

Art.Nr. DC-11202-1	EAN-Nr. 4016032222637	USB-PS/2 Combo-KVM Switch 1User, 2PCs
Art.Nr. DC-12202-1	EAN-Nr. 4016032222644	USB-PS/2 Combo-KVM Switch 1User, 4PCs
Art.Nr. DC-11401-1	EAN-Nr. 4016032222651	USB-PS/2 Combo-KVM Switch 1User, 2PCs with Audio
Art.Nr. DC-12401-1	EAN-Nr. 4016032222668	USB-PS/2 Combo-KVM Switch 1User, 4PCs with Audio