



Blackburn®

Power Distribution Blocks T&B Catalog Number:

UPC Number: PDS2440
Status: 78378647379
Description: Active

Tapping Power Distribution Block, Color: Gray, 1 Wire: Cu / Al 4/0 - #4 Awg, 2 Wires: Cu Only #2 - #6 Awg, 3 Wires: Cu Only #6 Awg, Voltage Rating: 600 Volts Max, Terminal Block Supplied

Features

Insulated housing provides fast, clean, safe installation and controlled dielectric strength. Easily installed and position-locked with DIN rail or screw mounting.

Grooved contact surfaces penetrate conductor oxides for best contact.

General

Style	Tapping Block
Color	Gray
Mounting Method	Top Hat rail or Screw
Wire Range	4/0 - 4 AWG
Screw Size	5mm
Maximum Current	230A CU/180A Al
Tightening Torque	126 lb.-in.

Dimension Information

Width (inches)	1.7
Height (inches)	3.4
Depth (inches)	1.9

Specifications

Temperature Rating	80°C Max
Voltage Rating	600 Volts Max.
Flamability Rating	UL 94 V-2

Packaging

T&B Order Multiple	3
T&B Inner Pack	3
Package in Units	30
T&B Sold in UOM	Each
T&B Weight Per UOM	282 lbs. per 1000

Application Support

T&B Sales Drawings	wsd-000215
Overview	Available on Website
Conductor Table	Available on Website

Certifications



File Nbr:
E66436

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com