

NOTES:

① MAT'L: COPPER (STOCK TKN $\frac{.031}{.79}$)
PLATING: ELECTRO-TIN (.0003 MIN.)

② BRAZED SEAM


STUD SIZES: ($\pm .005$)

02 = .094
04 = .119
06 = .146
08 = .173
10 = .198
14 = .265
56 = .328
38 = .390

"UL" LISTING #E32244
"CSA" LISTING #18689

ALL DIMENSIONS = INCHES
M M

WIRE SIZE: 16-14 AWG
1.0-2.5 MM²



FILE NO.

B-CD-301-01

PART NUMBER	"W" $\pm .010$	"C" MIN.	"L" MAX.	AVAILABLE STUD SIZES	TITLE:
B-318-	$\frac{.534}{13.56}$	$\frac{.554}{14.07}$	$\frac{1.115}{28.32}$	10, 14, 56, 38	RING TONGUE TERMINAL
B-323-	$\frac{.250}{6.35}$	$\frac{.209}{5.31}$	$\frac{.639}{16.23}$	02, 04, 06, 08	VERSAKRIMP 300-SERIES
B-325-	$\frac{.467}{11.86}$	$\frac{.388}{9.86}$	$\frac{.916}{23.27}$	10, 14, 56	
B-337-	$\frac{.312}{7.92}$	$\frac{.285}{7.24}$	$\frac{.730}{18.54}$	04, 06, 08, 10	
B-339-	$\frac{.342}{8.69}$	$\frac{.310}{7.87}$	$\frac{.775}{19.69}$	04, 06, 08, 10	
DIMENSIONAL TOLERANCES UNLESS OTHERWISE SPECIFIED					SCALE: NTS
FRAC.	DEC.	ANG.	REFERENCE	DATE	DWG. NO.
$\pm$	$\pm$	$\pm$		11/28/84	A
				CHKD. BY: GZ	CUSTOMER DWG.
				APPRD. BY:	

ETC
INCORPORATED

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[19056-0059](#)