

Direct Links

Cross Reference

RoHS/LF P/N search

Document & Drawing search

Application tooling

Services

Contact us

Distributor list

Pricing request

Order samples

Literature

Brochures & catalogs

Product documentation

Technical library

HLEM22S-1RLF

[Assistant](#) [Add to Favorites](#)



HLEM22S-1RLF - FPC/FFC,DII

HLEM S Series, 22 Pos, Top Entry Non ZIF Connector, 1.25 mm (0.049 in.), Lead Free

ACTIVE

[Customer Drawing](#)



Electronics division

☒ [Email Datasheet](#) ☐ [Print Datasheet](#)

FCI Brings You More

- ☒ [Contact our sales/technical support](#)
- ☒ [Sample request](#)
- ☒ [Price request](#)
- ☒ [Check distributor stock](#)

Download document

Technical Resources

Literature

Application Tooling

- ☒ > [RoHS qualification documents](#)

☒ > [Product Specification](#)
- ☒ > [Connector Overview Brochure](#)

☒ > [Flexible circuit connectors](#)
- ☒ > [Asia Pacific Application Tooling](#)

☒ > [Americas Application Tooling](#)

☒ > [Europe Application Tooling](#)

Specifications

General	Electrical	Mechanical	Mounting	Physical	Approvals / Certifications	Other Features
<u>General</u>						
Cable Insertion					Non - ZIF	
Number of contacts					22	
Orientation					Straight	
<u>Electrical</u>						
Withstanding Voltage					500V AC for 1 minute	
Current rating					1A AC/DC	
Resistance (Contact)					30 milli ohms max	
Resistance (Insulation)					1000 M- ohms min.	
Voltage rating					200V AC/DC	
<u>Mechanical</u>						
Durability (Mating cycles)					30 Cycles	
<u>Mounting</u>						
Mounting style (Board)					DIF	
<u>Physical</u>						
Cable Type					FPC/FFC	
Material (Contact)					Phosphor Bronze, Tin PrePlated	
Material (Housing)					Glass Reinforced PBT, UL94 V0	
Temperature (Range)					-55°C to +85°C	
<u>Approvals / Certifications</u>						
Damp Heat per JIS C 0022					Contact Resistance 50 milli ohms max	
Salt Spray per JIS C 0023					Contact Resistance 50 milli ohms max	
Temperature Cycling per JIS C 0025					Contact Resistance 50 milli ohms max	
Vibration per JIS C 0040					No Discontinuity > 1μ second	
<u>Other Features</u>						
Packaging (Type)					Tray	