


3.5mm 4 Cond In-Line Jack

161-6435-EX



3.5mm 4 Cond In-Line Jack



DIMENSIONS: mm (in.)

ELECTRICAL SPECIFICATIONS	
Dielectric Strength:	500V AC for one minute.
Contact Resistance:	50m Ohm Max.
Insulation Resistance:	100M Ohm Min. at 500V DC.

MATERIAL SPECIFICATIONS				
LET	Part Name	Material	Qty.	Finish
1	Housing	PA	1	
2	Sleeve	BSBM	1	Ni
3	Contact 1	FAB-EH t=0.25	1	Ni
4	Contact 2	FAB-EH t=0.25	1	Au
5	Contact 3	FAB-EH t=0.25	1	Ni
6	Contact 4	BSR t=0.3	1	Ni
7	Insulation Tube	PVC	1	
8	Handle	PE	1	
Mating plug:		171-7435-EX		
RoHS Compliant by Exemption				

Date Last Revised: 11-22-10

Available from Mouser Electronics
1-800-346-6873
www.mouser.com

KC-300960

161-6435-EX

Specifications are subject to change without notice. No liability or warranty implied by this information. Environmental compliance based on producer documentation.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[161-6435-EX](#)