


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PART NO.	LEGEND	HEIGHT "A"	WIDTH "B" (+/- .062)	LEGEND HEIGHT "C"	COLOR (LEGEND/ BACKGROUND)	MARKERS PER CARD	STD. PKG. QTY. CARD(S)
PVL100BY-0-Y	0	1.50 (.38.1)	0.900 (.22.9)	1.00 (.25.4)	BLACK/ YELLOW	10	25
PVL100BY-1-Y THRU PVL100BY-9-Y	1 THRU 9	1.50 (.38.1)	0.900 (.22.9)	1.00 (.25.4)	BLACK/ YELLOW	10	25
PVL100BY-A-Y THRU PVL100BY-Z-Y	A THRU Z	1.50 (.38.1)	0.900 (.22.9)	1.00 (.25.4)	BLACK/ YELLOW	10	25
PVL100BY-DSH-Y	- (DASH)	1.50 (.38.1)	0.900 (.22.9)	1.00 (.25.4)	BLACK/ YELLOW	10	25
PVL200BY-0-Y	0	2.25 (.57.2)	0.900 (.22.9)	2.00 (.50.8)	BLACK/ YELLOW	10	25
PVL200BY-1-Y THRU PVL200BY-9-Y	1 THRU 9	2.25 (.57.2)	0.900 (.22.9)	2.00 (.50.8)	BLACK/ YELLOW	10	25
PVL200BY-A-Y THRU PVL200BY-Z-Y	A THRU Z	2.25 (.57.2)	0.900 (.22.9)	2.00 (.50.8)	BLACK/ YELLOW	10	25
PVL200BY-DSH-Y	- (DASH)	2.25 (.57.2)	0.900 (.22.9)	2.00 (.50.8)	BLACK/ YELLOW	10	25

NOTE:
1. MILLIMETERS ARE IN [].



										CAD FILENAME/LAYERS					
										100569AK-DC-C10500/06F					
										PANDUIT CORP. TINLEY PARK, ILLINOIS					
										CUSTOMER DRAWING					
										VINYL LETTERS AND NUMBERS					
										PVL100BY-*** AND PVL200BY-***					
										UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± .12 (.XXX) ± .025 (.XX) ± .062 ANGLES ± 5°					
										UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.					
5	1/14/11	JHAC		Width should be .900" and legend height for the 1200 parts should be 2", not 1". UPDATE TABLE. ADD 9.25 WIDTH.				6280	R		DRAWN BY RVU	MAT'L:	SCALE NTS		
4	04/29/09	JHAC		CHANGED TOLERANCE ON DIM "B" TO +/- .062				5737	R			DATE 9-15-06	GMV1-OL FILM VINYL	DRAWING NO. C10500	DWG A
REV	DATE	BY	CHK	DESCRIPTION				ECN	R	CUST	SUP	CHK'D			SIZE