

Heavy Duty Adjustable Wall Bracket *APB Series*

Features



- Constructed in 14-gauge steel.
- EIA-310-D compliant 10-32 tapped rails with 19" mounting.
- Double-hinged for easy rear access.
- Adjustable depth from 12" to 18" using slots for easy set-up and adjusting.
- **If you are looking for a taller or deeper option consider the New HWMR Series.**
- Rear cable access with multiple tie points for cable management.
- Finished in textured black powder paint.
- Ships un-assembled in a flat pack container for easy handling and shipping protection.
- Includes starter pack of mounting hardware. (25-pack of 10-32 screws)
- Tested to nearly double the suggested load rating of 80 lbs.
- RoHS Compliant.
- Manufactured in North America.

Gallery



Accessories

[Two Post Mounting Cantilever Shelf](#)

[Cable Management](#)

[Mounting Hardware](#)

• [Two Post Mounting Keyboard & Monitor Shelf](#)

• [Outlet Strips](#)

• [Rack Panels](#)

Part No.	Overall Dimensions		Mounting Dimensions				Rack Shipping	
	Height	Width	Height	Width	Min Depth	Max Depth	Units	Weight
APB19007BK1	6.98	19.25	7.00	19.00	12.00	18.00	4U	10.3
APB19010BK1	10.48	19.25	10.50	19.00	12.00	18.00	6U	15
APB19014BK1	13.98	19.25	14.00	19.00	12.00	18.00	8U	20.5
APB19021BK1	20.98	19.25	21.00	19.00	12.00	18.00	12U	30

Shelf/Cover for APB and HPB

Part No.	Overall Dimensions		
	Height	Width	Depth
PBCOVER	0.50	19.25	6.00

Data subject to change without notice.

© 2013. Hammond Manufacturing Ltd. All rights reserved.